

## RA N Male to RA N Male Cable Tinned Aluminum RG405 Type .086 Coax in 60 Inch

The RA type N male to RA type N male 60 inch cable using Tinned Aluminum RG405 type .086 coax, part number FMCA2997-60, from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N cable assembly has a male to male gender configuration with 50 ohm semi-rigid FM-SR086ALTN-STR coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA2997-60 type N male to type N male cable assembly operates to 11 GHz. The right angle type N interfaces on the FM-SR086ALTN-STR cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

| Description     | Min | Typ | Max   | Units |
|-----------------|-----|-----|-------|-------|
| Frequency Range | DC  |     | 11    | GHz   |
| VSWR            |     |     | 1.5:1 |       |

### Performance by Frequency

| Description           | F1   | F2   | F3   | F4  | F5 | Units |
|-----------------------|------|------|------|-----|----|-------|
| Frequency             | 1    | 2.5  | 5    | 11  |    | GHz   |
| Insertion Loss (Typ.) | 1.55 | 2.03 | 2.84 | 4.7 |    | dB    |

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.2 dB per connector.

### Mechanical Specifications

#### Cable Assembly

|         |                    |
|---------|--------------------|
| Length* | 60 in [152.4 cm]   |
| Weight  | 0.19 lbs [86.18 g] |

#### Cable

|                                      |                           |
|--------------------------------------|---------------------------|
| Cable Type                           | FM-SR086ALTN-STR          |
| Impedance                            | 50 Ohms                   |
| Inner Conductor Type                 | Solid                     |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type                      | PTFE                      |
| Number of Shields                    | 1                         |
| Outer Conductor Material and Plating | Tinned Aluminum           |

|                              |                   |
|------------------------------|-------------------|
| One Time Minimum Bend Radius | 0.05 in [1.27 mm] |
|------------------------------|-------------------|



### Configuration:

- N Male Right Angle
- N Male Right Angle
- FM-SR086ALTN-STR

### Features:

- Max Frequency 11 GHz

### Applications:

- General Purpose
- Laboratory Use

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Connectors

| Description                     | Connector 1   | Connector 2   |
|---------------------------------|---------------|---------------|
| Type                            | N Male        | N Male        |
| Impedance                       | 50 Ohms       | 50 Ohms       |
| Contact Material & Plating      | Brass, Gold   | Brass, Gold   |
| Dielectric Type                 | PTFE          | PTFE          |
| Body Material & Plating         | Brass, Nickel | Brass, Nickel |
| Coupling Nut Material & Plating | Brass, Nickel | Brass, Nickel |

## Compliance Certifications (see [product page](#) for current document)

## Plotted and Other Data

Notes:

## How to Order

Part Number Configuration:

**FMCA2997 - xx uu**

cm = Centimeters  
 <blank> = Inches

Length

Example: FMCA2997-12 = 12 inches long cable  
 FMCA2997-100cm = 100 cm long cable

RA N Male to RA N Male Cable Tinned Aluminum RG405 Type .086 Coax in 60 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [RA N Male to RA N Male Cable Tinned Aluminum RG405 Type .086 Coax in 60 Inch FMCA2997-60](#)

URL: <https://www.fairviewmicrowave.com/ra-n-male-to-ra-n-male-cable-rg405-type-.086-coax-fmca2997-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

REVISIONS

| REV. | DESCRIPTION     | DATE       | APPROVED |
|------|-----------------|------------|----------|
| A    | INITIAL RELEASE | 08/02/2022 | AGANWANI |

LENGTH MEASURED FROM CONTACT TO CONTACT

FM-SR086ALTN-STR

WWW.FAIRVIEWMICROWAVE.COM  
FAIRVIEW MICROWAVE P/N  
(SEE NOTE 1)

N MALE  
RIGHT ANGLE

N MALE  
RIGHT ANGLE

NOTES:

1. CABLES 36" AND UNDER HAVE 1 LABEL CENTERED.  
CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH END  
6.0" FROM THE FRONT OF THE CONNECTOR.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT  
ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

Fairview Microwave

an INFINITE brand

TITLE

RA N Male to RA N Male Cable Tinned Aluminum  
RG405 Type .086 Coax in 60 Inch

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:

CABLE LENGTH (L) TOLERANCES:

.X = ±.2 [ .508 ] FRACTIONS  
.XX = ±.02 [ .51 ] ± 1/32  
.XXX = ±.005 [ .13 ] ANGLES ± 1°

L ≤ 12 [ 305 ] = +1 [ 25 ] / -0  
12 [ 305 ] < L ≤ 60 [ 1524 ] = +2 [ 51 ] / -0  
60 [ 1524 ] < L ≤ 120 [ 3048 ] = +4 [ 102 ] / -0  
120 [ 3048 ] < L ≤ 300 [ 7620 ] = +6 [ 152 ] / -0  
300 [ 7620 ] < L = +5%L / -0

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

SIZE  
A

CAGE CODE  
3FKR5

DRAWN BY  
PSRINIVAS

ITEM NO.  
FMCA2997

REV  
A

THIRD-ANGLE PROJECTION

THE INFORMATION AND  
DESIGN IN THIS DOCUMENT  
IS THE PROPERTY OF  
FAIRVIEW MICROWAVE CORPORATION.  
ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020

REV 1.0 Page 3 of 3