

3.5mm Male to 3.5mm Male Cable Tinned Copper RG405 Type .086 Coax in 60 Inch

The 3.5mm male to 3.5mm male 60 inch cable using Tinned Copper RG405 type .086 coax, part number FMCA3038-60, from Fairview Microwave is in-stock and ships same day. This Fairview 3.5mm to 3.5mm cable assembly has a male to male gender configuration with 50 ohm semi-rigid FM-SR086CUTN-STR coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Mechanical Specifications

Cable Assembly

Length*	60 in [152.4 cm]
Weight	0.097 lbs [44 g]

Cable

Cable Type	FM-SR086CUTN-STR
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Tinned Copper

One Time Minimum Bend Radius	0.05 in [1.27 mm]
------------------------------	-------------------

Connectors

Description	Connector 1	Connector 2
Type	3.5mm Male	3.5mm Male
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold over Nickel
Contact Plating Spec.	50 µin minimum	50 µin minimum
Dielectric Type	PCTFE	PCTFE
Body Material & Plating	Passivated Stainless Steel	Passivated Stainless Steel
Body Plating Spec.	SAE-AMS-2700	SAE-AMS-2700
Coupling Nut Material & Plating	Passivated Stainless Steel	Passivated Stainless Steel
Coupling Nut Plating Spec.	SAE-AMS-2700	SAE-AMS-2700
Hex Size	5/16 inch	5/16 inch
Torque	8 in-lbs 0.9 Nm	8 in-lbs 0.9 Nm



Configuration:

- 3.5mm Male
- 3.5mm Male
- FM-SR086CUTN-STR

Applications:

- General Purpose
- Laboratory Use

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMCA3038 - xx uu

cm = Centimeters
<blank> = Inches

Length

Example: FMCA3038-12 = 12 inches long cable
FMCA3038-100cm = 100 cm long cable


3.5mm Male to 3.5mm Male Cable Tinned Copper RG405 Type .086 Coax in 60 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [3.5mm Male to 3.5mm Male Cable Tinned Copper RG405 Type .086 Coax in 60 Inch FMCA3038-60](#)

URL: <https://www.fairviewmicrowave.com/3.5mm-male-to-3.5mm-male-cable-tinned-copper-rg405-type-.086-coax-fmca3038-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/04/22	AGANWANI



NOTES:

1. CABLES 36" AND UNDER HAVE 1 LABEL CENTERED.
CABLES OVER 36" HAVE 2 LABELS, ONE AT EACH END
6.0" FROM THE FRONT OF THE CONNECTOR.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

<div><div><div></div><div></div><div></div><div></div></div><div><div></div><div></div><div></div><div></div></div></div> <div><div>Fairview Microwave</div><div>an INFINITI® brand</div></div>		<div>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS</div> <div><div>TOLERANCES:</div><div><div>.X = ±.2 [.508]</div><div>FRACTIONS</div><div>12 [305] < L ≤ 60 [1524] = +.2 [5.1] / -0</div></div><div><div>.XX = ±.02 [.51]</div><div>± 1/32</div><div>60 [1524] < L ≤ 120 [3048] = +.4 [10.2] / -0</div></div><div><div>.XXX = ±.005 [.13]</div><div>ANGLES ± 1°</div><div>120 [3048] < L ≤ 300 [7620] = +.6 [15.2] / -0</div></div><div><div>300 [7620] < L = +5%L / -0</div></div></div>				<div>THIRD-ANGLE PROJECTION</div> <div><div><div></div><div></div></div><div>THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.</div></div> <div><div>SHEET</div><div>1</div><div>OF</div><div>1</div></div>	
TITLE		ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.					
3.5mm Male to 3.5mm Male Cable Tinned Copper RG405 Type .086 Coax in 60 Inch		SCALE N/A					
SIZE A	CAGE CODE 3FKR5	DRAWN BY VTHANGARAJ	ITEM NO. FMCA3038	REV A			

T-Rev.D