

## Low Loss N Male to RA N Male Cable

### TCOM-240 Coax in 12 Inch with Times Microwave Components

The type N male to RA type N male 12 inch cable using TCOM-240 coax, part number FMCA3278-12, from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N cable assembly has a male to male gender configuration with 50 ohm flexible TCOM-240 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA3278-12 type N male to type N male cable assembly operates to 6 GHz. The right angle type N interface on the TCOM-240 cable allows for easier connections in tight spaces. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### Electrical Specifications

| Description     | Min | Typ | Max   | Units |
|-----------------|-----|-----|-------|-------|
| Frequency Range | DC  |     | 6     | GHz   |
| VSWR            |     |     | 1.4:1 |       |

### Performance by Frequency

| Description           | F1   | F2  | F3   | F4   | F5   | Units |
|-----------------------|------|-----|------|------|------|-------|
| Frequency             | 0.25 | 0.5 | 1    | 2.5  | 6    | GHz   |
| Insertion Loss (Typ.) | 0.14 | 0.2 | 0.28 | 0.44 | 0.69 | dB    |

### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of  $0.1 \times \sqrt{F(\text{GHz})}$  dB per connector

### Mechanical Specifications

#### Cable Assembly

|         |                    |
|---------|--------------------|
| Length* | 12 in [304.8 mm]   |
| Weight  | 0.209 lbs [94.8 g] |

#### Cable

|                                      |                            |
|--------------------------------------|----------------------------|
| Cable Type                           | TCOM-240                   |
| Impedance                            | 50 Ohms                    |
| Inner Conductor Type                 | Solid                      |
| Inner Conductor Material and Plating | Copper                     |
| Dielectric Type                      | PE (F)                     |
| Number of Shields                    | 2                          |
| Shield Layer 1                       | Silver Plated Copper Braid |
| Shield Layer 2                       | Tinned Copper Braid        |
| Jacket Material                      | PE, Black                  |
| Jacket Diameter                      | 0.24 in [6.1 mm]           |



### Configuration:

- N Male
- N Male Right Angle
- TCOM-240

### Features:

- Max Frequency 6 GHz
- Double Shielded
- PE Jacket
- 500 Mating Cycles

### Applications:

- General Purpose
- Laboratory Use

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Connectors

| Description                     | Connector 1            | Connector 2            |
|---------------------------------|------------------------|------------------------|
| Type                            | N Male Threaded        | N Male Threaded        |
| Specification                   | MIL-STD-348            |                        |
| Impedance                       | 50 Ohms                | 50 Ohms                |
| Mating Cycles                   | 500                    | 500                    |
| Contact Material & Plating      | Beryllium Copper, Gold | Beryllium Bronze, Gold |
| Contact Plating Spec.           | ASTM-B488              | 50 µin minimum         |
| Dielectric Type                 | Teflon                 | PTFE                   |
| Body Material & Plating         | Brass, Tri-Metal       | Brass, Tri-Metal       |
| Body Plating Spec.              | QQ-N-290               | 80 µin minimum         |
| Coupling Nut Material & Plating | Brass, Tri-Metal       | Brass, Tri-Metal       |
| Coupling Nut Plating Spec.      | QQ-N-290               | 80 µin minimum         |

**Compliance Certifications** (see [product page](#) for current document)

## Plotted and Other Data

Notes:

## How to Order

Part Number Configuration:

**FMCA3278 - xx uu**

cm = Centimeters  
 <blank> = Inches

Length

Example: FMCA3278-12 = 12 inches long cable  
 FMCA3278-100cm = 100 cm long cable

Low Loss N Male to RA N Male Cable TCOM-240 Coax in 12 Inch with Times Microwave Components from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Low Loss N Male to RA N Male Cable TCOM-240 Coax in 12 Inch with Times Microwave Components FMCA3278-12](#)

URL: <https://www.fairviewmicrowave.com/low-loss-n-male-to-ra-n-male-cable-tcom-240-coax-in-12-inch-with-times-microwave-components-fmca3278-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

