

Low Loss TNC Male to TNC Female
Cable TCOM-240 Coax in 24 Inch with
Times Microwave Components




FMCA3287-24

Configuration

- Connector 1: TNC Male
- Connector 2: TNC Female
- Cable Type: TCOM-240
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- Double Shielded
- PE Jacket
- 500 Mating Cycles



Applications

- General Purpose
- Laboratory Use

Description

The TNC male to TNC female 24 inch cable using TCOM-240 coax, part number FMCA3287-24, from Fairview Microwave is in-stock and ships same day. This Fairview TNC to TNC cable assembly has a male to female gender configuration with 50 ohm flexible TCOM-240 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA3287-24 TNC male to TNC female cable assembly operates to 6 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	6	GHz
Insertion Loss (Typ.)	0.37	0.42	0.49	0.71	0.88	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1*SQRT(FGHz) dB for the TNC male connector and 0.24 dB for the TNC female connector.

Low Loss TNC Male to TNC Female
Cable TCOM-240 Coax in 24 Inch with
Times Microwave Components



FMCA3287-24

Mechanical Specifications

Cable Assembly

Length	24 in [609.6 mm]
Width/Diameter	0.5 in [12.7 mm]
Weight	0.21 lbs [95.25 g]

Cable

Cable Type	TCOM-240
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.24 in [6.1 mm]

Connectors

Description	Connector 1	Connector 2
Type	TNC Male	TNC Female
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Mating Cycles	500	500
Contact Material and Plating	Phosphor Bronze, Gold	Brass, Tri-Metal
Contact Plating Specification	50µ in. minimum	80 µin minimum
Dielectric Type	Teflon	PTFE
Outer Conductor Material and Plating		Brass, Tri-Metal
Outer Conductor Plating Specification		80 µin minimum
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	80µ in. minimum	80 µin minimum
Coupling Nut Material and Plating	Brass, Tri-Metal	
Coupling Nut Plating Specification	80µ in. minimum	

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Low Loss TNC Male to TNC Female
Cable TCOM-240 Coax in 24 Inch with
Times Microwave Components




FMCA3287-24

Typical Performance Data

How to Order

Part Number Configuration:



Example: FMCA3287-12 = 12 inches long cable
FMCA3287-100cm = 100 cm long cable

Low Loss TNC Male to TNC Female Cable TCOM-240 Coax in 24 Inch with Times Microwave Components from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Low Loss TNC Male to TNC Female Cable TCOM-240 Coax in 24 Inch with Times Microwave Components FMCA3287-24](https://www.fairviewmicrowave.com/low-loss-tnc-male-to-tnc-female-cable-tcom-240-coax-in-24-inch-with-times-microwave-components-fmca3287-24)

URL: <https://www.fairviewmicrowave.com/low-loss-tnc-male-to-tnc-female-cable-tcom-240-coax-in-24-inch-with-times-microwave-components-fmca3287-24-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA3287-24 CAD Drawing

Low Loss TNC Male to TNC Female Cable TCOM-240 Coax in 24 Inch with Times Microwave Components

