

VITA 67 Mini SMP Female to 2.92mm Male Cable FM-F086HF Coax in 6 Inch

FMCA9742-6



Configuration

- Connector 1: Mini SMP Female
- Connector 2: 2.92mm Male
- Cable Type: FM-F086HF
- Coax Cable Group: 2
- Coax Flex Type: Flexible

Features

- Max Frequency 40 GHz
- Shielding Effectivity > 110 dB
- 70% Phase Velocity
- Standard MIL-STD-348 SMPM interface
- Push-on/snap-on mating style for quick installation
- Mini SMP (SMPM) Female compatible with VITA 67 (4-port) and (8-port) blocks
- Mini SMP (SMPM) Male Compatible with VITA 67 (4-port) and (8-port) blocks

Applications

- General Purpose
- Laboratory Use
- Scientific research
- High-reliability, high-density for aerospace & defense application
- Ground base station & communication systems, avionics, radar systems

Description

The Mini SMP female to 2.92mm male 6 inch cable using FM-F086HF coax, part number FMCA9742-6, from Fairview Microwave is in-stock and ships same day. This Fairview Mini SMP to 2.92mm cable assembly has a female to male gender configuration with 50 ohm flexible coax. Fairview Microwave's VITA 67 assemblies are high-density, high-performance, fixed-length RF cable assemblies that fit into VITA 67 blocks and attach to the PCB board which makes it ideal for applications where tight bends and flexure is required. The FMCA9742-6 Mini SMP female to 2.92mm male cable assembly operates to 40 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
VSWR			1.14:1	
Velocity of Propagation		70		%
RF Shielding	110			dB

VITA 67 Mini SMP Female to 2.92mm Male
Cable FM-F086HF Coax in 6 Inch

FMCA9742-6



Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Capacitance		29.4 [96.46]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	2.5	5	10	20	40	GHz
Insertion Loss (Typ.)	0.38	0.46	0.58	0.73	1.06	dB

Electrical Specification Notes:
Values at 25°C, sea level.

Mechanical Specifications

Cable Assembly

Length 6 in [152.4 mm]
Weight 0.22 lbs [99.79 g]

Cable

Cable Type FM-F086HF
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper Clad Steel, Silver
Dielectric Type PTFE
Shield Layer 1 Silver Plated Copper Tape

Connectors

Description	Connector 1	Connector 2
Type	Mini SMP Female	2.92mm Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold over Nickel
Contact Plating Specification	ASTM B488	50 µin minimum
Dielectric Type		PEI
Body Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold over Nickel
Body Plating Specification	ASTM B488	50 µin minimum

VITA 67 Mini SMP Female to 2.92mm Male Cable FM-F086HF Coax in 6 Inch



FMCA9742-6

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

Typical Performance Data

How to Order

Part Number Configuration:

FMCA9742 **- xx** **uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: FMCA9742-12 = 12 inches long cable
FMCA9742-100cm = 100 cm long cable

VITA 67 Mini SMP Female to 2.92mm Male Cable FM-F086HF Coax in 6 Inch from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: [VITA 67 Mini SMP Female to 2.92mm Male Cable FM-F086HF Coax in 6 Inch FMCA9742-6](#)

URL: <https://www.fairviewmicrowave.com/vita-67-mini-smp-female-to-2.92mm-male-cable-fm-f086hf-coax-in-6-inch-fm-ca9742-6-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA9742-6 CAD Drawing

VITA 67 Mini SMP Female to 2.92mm Male Cable FM-F086HF Coax in 6 Inch



REVISION		DATE	CHANGED BY	APPROVED
ZONE	REV			
	B	12/20/2023	DMAY	AGANWANI
DESCRIPTION		UPDATED PER ECO-13165		

Fairview Microwave® an INFINITI® brand		Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.972.649.6678		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN INCHES. DIMENSIONS IN [] ARE MILLIMETERS.		TOLERANCES:		SCALE: NONE
X = ±.2 [5]		FRACTIONS		SHEET: 1 OF 1
.XX = ±.02 [0.5]		± 1/32		
.XXX = ±.005 [0.13]		ANGLES ± 1°		
CABLE LENGTH TOLERANCES:		±.12 [3.05]		
>12 [305] ≤ 60 [1524] = ±.12 [3.05]		±.12 [3.05]		
>60 [1524] ≤ 120 [3048] = ±.12 [3.05]		±.12 [3.05]		
>120 [3048] ≤ 300 [7620] = ±.12 [3.05]		±.12 [3.05]		
ALL DIMENSIONS ARE FOR REFERENCE ONLY. DIMENSIONS SHALL BE TO THE CENTER OF THE CABLE UNLESS OTHERWISE SPECIFIED. DIMENSIONS MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.		DESCRIPTION		
		MINI SMP FEMALE VITA 67 CONNECTOR TO 2.92mm MALE CABLE USING FM-F086HF COAX		
SIZE		CAGE CODE	DRAWN BY	REV
A	3FKR5	DMAY	1	B
		ITEM NO.	FMCA9742	