

20KV Female Bulkhead to MHV Female 4 Hole Flange Cable RG213HV Coax



FMCA9786

Configuration

- Connector 1: 20KV Female Bulkhead
- Connector 2: MHV Female 4 Hole Flange
- Cable Type: RG213HV

Features

- 69% Phase Velocity
- polyurethane Jacket

Applications

- General Purpose
- Laboratory Use

Description

The 20KV female bulkhead to MHV female 4 hole flange cable using RG213HV coax, part number FMCA9786, from Fairview Microwave is in-stock and ships same day. This Fairview 20KV to MHV cable assembly has a female to female gender configuration with 50 ohm RG213HV coax. Our RF cable assembly with 20KV bulkhead and MHV 4 hole flange interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. Our 20kV high voltage RF cable assemblies are designed to handle higher voltages and minimize the risk of electric shock. Both the connectors used in this cable assemblies have recessed contact design to withstand unmated higher voltage. These cable assemblies are commonly used in applications where high voltage transmission and RF signal integrity are critical. These cable assemblies are constructed with high-quality insulation materials capable of withstanding higher voltages, ensuring safety and preventing electrical breakdown. Our cable assemblies are built with durable and flexible materials to withstand harsh environmental conditions and repetitive movements, ensuring reliable performance over extended periods.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------|---------|---------|---------|-------|
| Velocity of Propagation | | 69 | | % |

Electrical Specification Notes:
Values at 25°C, sea level.

Mechanical Specifications

Cable Assembly

| | |
|----------------|---------------------|
| Width/Diameter | 0.5 in [12.7 mm] |
| Weight | 0.31 lbs [140.61 g] |

Cable

| | |
|--------------------------------------|--------------|
| Cable Type | RG213HV |
| Impedance | 50 Ohms |
| Inner Conductor Material and Plating | Copper, Bare |

20KV Female Bulkhead to MHV Female
4 Hole Flange Cable RG213HV Coax



FMCA9786

| | |
|------------------------------|---------------------|
| Dielectric Type | PE |
| Number of Shields | 1 |
| Jacket Material | polyurethane |
| Jacket Diameter | 0.394 in [10.01 mm] |
| Repeated Minimum Bend Radius | 1.969 in [50.01 mm] |

Connectors

| Description | Connector 1 | Connector 2 |
|-----------------------------------|----------------------------------|--------------------------|
| Type | 20KV Female Bulkhead | MHV Female 4 Hole Flange |
| Specification | MIL-STD-202 | MIL-STD-348 |
| Impedance | 50 Ohms | 50 Ohms |
| Configuration | Straight | Straight |
| Contact Material and Plating | Beryllium Copper, Gold/Tri-Metal | Silver |
| Contact Plating Specification | | QQ-S-365 |
| Dielectric Type | PE (HD) | PTFE |
| Body Material and Plating | Brass, Nickel Over Copper | Brass, Nickel |
| Body Plating Specification | | QQ-N-290 |
| Coupling Nut Material and Plating | Brass, Nickel Over Copper | |

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

20KV Female Bulkhead to MHV Female 4 Hole Flange Cable RG213HV Coax



FMCA9786

Typical Performance Data

How to Order

Part Number Configuration:

FMCA9786

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: FMCA9786-12 = 12 inches long cable
FMCA9786-100cm = 100 cm long cable

20KV Female Bulkhead to MHV Female 4 Hole Flange Cable RG213HV Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [20KV Female Bulkhead to MHV Female 4 Hole Flange Cable RG213HV Coax FMCA9786](#)

URL: <https://www.fairviewmicrowave.com/20kv-female-bulkhead-to-mhv-female-4-hole-flange-cable-rg213hv-coax-fm-ca9786-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA9786 CAD Drawing
20KV Female Bulkhead to MHV Female 4 Hole Flange Cable RG213HV Coax

