

## MCX Plug to MCX Plug using RG316 Coax Cable in 24 Inches

### FMCA9840-24




#### Configuration

- Connector 1: MCX Plug
- Connector 2: MCX Plug
- Cable Type: RG316

#### Features

- Max Frequency 3 GHz
- 69% Phase Velocity
- VSWR of 1.4:1



#### Applications

- General Purpose
- Laboratory Use
- Military
- Aerospace
- Wireless Communications
- General Purpose Test

#### Description

The MCX plug to MCX plug 24 inch cable using RG316, part number FMCA9840-24, from Fairview Microwave is in-stock and ships same day. This Fairview MCX to MCX cable assembly has a plug to plug gender configuration with 50 ohm RG316. The FMCA9840-24 MCX plug to MCX plug cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

| Description             | Minimum | Typical      | Maximum | Units        |
|-------------------------|---------|--------------|---------|--------------|
| Frequency Range         | DC      |              | 3       | GHz          |
| VSWR                    |         |              | 1.4:1   |              |
| Velocity of Propagation |         | 69           |         | %            |
| Capacitance             |         | 29.4 [96.46] |         | pF/ft [pF/m] |

#### Specifications by Frequency

| Description           | F1   | F2   | F3   | F4   | F5   | Units |
|-----------------------|------|------|------|------|------|-------|
| Frequency             | 0.1  | 0.25 | 0.5  | 1    | 3    | GHz   |
| Insertion Loss (Typ.) | 0.42 | 0.52 | 0.68 | 0.96 | 1.36 | dB    |

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB per connector

## MCX Plug to MCX Plug using RG316 Coax Cable in 24 Inches

### FMCA9840-24



#### Mechanical Specifications

##### Cable Assembly

|                |                      |
|----------------|----------------------|
| Length         | 24 in [609.6 mm]     |
| Width/Diameter | 0.5 in [12.7 mm]     |
| Weight         | 0.0865 lbs [39.24 g] |

##### Cable

|                                      |                           |
|--------------------------------------|---------------------------|
| Cable Type                           | RG316                     |
| Impedance                            | 50 Ohms                   |
| Inner Conductor Type                 | Stranded                  |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type                      | PTFE                      |

#### Connectors

| Description                  | Connector 1                   | Connector 2                   |
|------------------------------|-------------------------------|-------------------------------|
| Type                         | MCX Plug                      | MCX Plug                      |
| Impedance                    | 50 Ohms                       | 50 Ohms                       |
| Configuration                | Straight                      | Straight                      |
| Contact Material and Plating | Bronze, Gold over Copper      | Bronze, Gold over Copper      |
| Body Material and Plating    | Bronze, Copper-Tin-Zinc Alloy | Bronze, Copper-Tin-Zinc Alloy |

#### Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:  
Values at 25°C, sea level.

## MCX Plug to MCX Plug using RG316 Coax Cable in 24 Inches

### FMCA9840-24



#### Typical Performance Data

#### How to Order

Part Number Configuration:

**FMCA9840**

**- xx**

**uu**

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: FMCA9840-12 = 12 inches long cable  
FMCA9840-100cm = 100 cm long cable

MCX Plug to MCX Plug using RG316 Coax Cable in 24 Inches from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [MCX Plug to MCX Plug using RG316 Coax Cable in 24 Inches FMCA9840-24](#)

URL: <https://www.fairviewmicrowave.com/non-magnetic-mcx-plug-to-mcx-plug-cable-rg316-coax-in-24-inch-fmca9840-24-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA9840-24 CAD Drawing

MCX Plug to MCX Plug using RG316 Coax Cable in 24 Inches

