

## SMB Plug to SMB Plug using RG316 Coax Cable in 24 Inches




### FMCA9849-24

#### Configuration

- Connector 1: SMB Plug
- Connector 2: SMB Plug
- Cable Type: RG316

#### Features

- Max Frequency 3 GHz
- 69% Phase Velocity
- VSWR of 1.4:1



#### Applications

- General Purpose
- Laboratory Use
- Military
- Aerospace
- Wireless Communications
- General Purpose Test

#### Description

The SMB plug to SMB plug 24 inch cable using RG316, part number FMCA9849-24, from Fairview Microwave is in-stock and ships same day. This Fairview SMB to SMB cable assembly has a plug to plug gender configuration with 50 ohm RG316. The FMCA9849-24 SMB plug to SMB plug cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		69		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.42	0.52	0.68	0.96	1.36	dB

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB per connector

## SMB Plug to SMB Plug using RG316 Coax Cable in 24 Inches



### FMCA9849-24

#### Mechanical Specifications

##### Cable Assembly

Length	24 in [609.6 mm]
Width/Diameter	0.5 in [12.7 mm]
Weight	0.168 lbs [76.2 g]

##### Cable

Cable Type	RG316
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE

#### Connectors

Description	Connector 1	Connector 2
Type	SMB Plug	SMB Plug
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Gold over Copper	Beryllium Copper, Gold over Copper
Body Material and Plating	Bronze, Copper-Tin-Zinc Alloy	Bronze, Copper-Tin-Zinc Alloy

#### Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:  
Values at 25°C, sea level.

## SMB Plug to SMB Plug using RG316 Coax Cable in 24 Inches



### FMCA9849-24

#### Typical Performance Data

#### How to Order

Part Number Configuration:

**FMCA9849**

**- xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: FMCA9849-12 = 12 inches long cable  
FMCA9849-100cm = 100 cm long cable

SMB Plug to SMB Plug using RG316 Coax Cable in 24 Inches from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [SMB Plug to SMB Plug using RG316 Coax Cable in 24 Inches FMCA9849-24](#)

URL: <https://www.fairviewmicrowave.com/non-magnetic-smb-plug-to-smb-plug-cable-rg316-coax-in-24-inch-fmca9849-24-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

# FMCA9849-24 CAD Drawing

SMB Plug to SMB Plug using RG316 Coax Cable in 24 Inches

