

BNC Plug Right Angle to BNC Plug using RG58 Coax Cable

FMCA9857



Configuration

- Connector 1: BNC Plug Right Angle
- Connector 2: BNC Plug

Features

- Max Frequency 4 GHz
- 65.9% Phase Velocity
- VSWR of 1.4:1

Applications

- General Purpose
- Laboratory Use
- Military
- Aerospace
- Wireless Communications
- General Purpose Test

Description

The RA BNC plug to BNC plug cable using RG58, part number FMCA9857, from Fairview Microwave is in-stock and ships same day. This Fairview BNC to BNC cable assembly has a plug to plug gender configuration with 50 ohm. The FMCA9857 BNC plug to BNC plug cable assembly operates to 4 GHz. The right angle BNC interface on the cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.4:1	
Velocity of Propagation		65.9		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	4	GHz
Insertion Loss (Typ.)	0.04	0.07	0.11	0.2	0.5	dB/ft
	0.13	0.23	0.36	0.66	1.64	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB per connector

Mechanical Specifications

Cable Assembly

Width/Diameter 0.5 in [12.7 mm]

BNC Plug Right Angle to BNC Plug using RG58 Coax Cable

FMCA9857



Weight	0.29 lbs [131.54 g]
Cable	
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Tin
Dielectric Type	PE
Number of Shields	1
Shield Layer 1	Tinned Copper Braid

Connectors

Description	Connector 1	Connector 2
Type	BNC Plug Right Angle	BNC Plug
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Contact Material and Plating	Bronze, Gold over Copper	Bronze, Gold over Copper
Body Material and Plating	Bronze, Copper-Tin-Zinc Alloy	Bronze, Copper-Tin-Zinc Alloy

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

BNC Plug Right Angle to BNC Plug using RG58 Coax Cable



FMCA9857

Typical Performance Data

How to Order

Part Number Configuration:

FMCA9857

- xx

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: FMCA9857-12 = 12 inches long cable
FMCA9857-100cm = 100 cm long cable

BNC Plug Right Angle to BNC Plug using RG58 Coax Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [BNC Plug Right Angle to BNC Plug using RG58 Coax Cable FMCA9857](#)

URL: <https://www.fairviewmicrowave.com/non-magnetic-ra-bnc-plug-to-bnc-plug-cable-rg58-coax-fmca9857-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA9857 CAD Drawing

BNC Plug Right Angle to BNC Plug using RG58 Coax Cable

