

## 4.3-10 Plug to 4.3-10 Plug Non-Magnetic Cable using 0.141 Formable Coax 48 Inches

### FMCA9858-48



#### Configuration

- Connector 1: 4.3-10 Plug
- Connector 2: 4.3-10 Plug
- Coax Flex Type: Formable

#### Features

- Max Frequency 6 GHz
- 70% Phase Velocity
- Magnetic Susceptibility  $10^{-5}$
- VSWR of 1.4:1

#### Applications

- General Purpose
- Laboratory Use
- Medical
- Quantum Computing
- Military
- Aerospace

#### Description

The 4.3-10 plug to 4.3-10 plug 48 inch cable using INVALID ALIAS LOOKUP FOR \*0.141\*, part number FMCA9858-48, from Fairview Microwave is in-stock and ships same day. This Fairview 4.3-10 to 4.3-10 cable assembly has a plug to plug gender configuration with 50 ohm formable. Fairview Microwave's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. The FMCA9858-48 4.3-10 plug to 4.3-10 plug cable assembly operates to 6 GHz. Fairview Microwave Non Magnetic connectors are manufactured with materials that are especially adapted to non magnetism. Our non-magnetic connectors have a higher magnetic susceptibility than existing standard connectors made of brass/nickel materials. As a result, our non-magnetic connectors are transparent to the magnetic field, which means no field distortion and a higher Signal-to-Noise Ratio (SNR).

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		70		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	6		GHz
Insertion Loss (Typ.)	0.64	0.84	1.16	1.92		dB

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB per connector

4.3-10 Plug to 4.3-10 Plug Non-Magnetic Cable  
using 0.141 Formable Coax 48 Inches

FMCA9858-48



Mechanical Specifications

Cable Assembly	
Length	48 in [121.92 cm]
Width/Diameter	0.5 in [12.7 mm]
Weight	0.23 lbs [104.33 g]
Cable	
Impedance	50 Ohms

Connectors

Description	Connector 1	Connector 2
Type	4.3-10 Plug	4.3-10 Plug
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Silver	Brass, Silver
Body Material and Plating	Brass, Copper-Tin-Zinc Alloy	Brass, Copper-Tin-Zinc Alloy

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:  
Values at 25°C, sea level.

## 4.3-10 Plug to 4.3-10 Plug Non-Magnetic Cable using 0.141 Formable Coax 48 Inches



### FMCA9858-48

#### Typical Performance Data

#### How to Order

Part Number Configuration:

**FMCA9858**

**- xx**

**uu**

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: FMCA9858-12 = 12 inches long cable  
FMCA9858-100cm = 100 cm long cable

4.3-10 Plug to 4.3-10 Plug Non-Magnetic Cable using 0.141 Formable Coax 48 Inches from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [4.3-10 Plug to 4.3-10 Plug Non-Magnetic Cable using 0.141 Formable Coax 48 Inches FMCA9858-48](#)

URL: <https://www.fairviewmicrowave.com/non-magnetic-4.3-10-plug-to-4.3-10-plug-cable-fm-141fl-nm-coax-in-48-inch-fmca9858-48-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA9858-48 CAD Drawing

4.3-10 Plug to 4.3-10 Plug Non-Magnetic Cable using 0.141 Formable Coax 48 Inches

