

## 1.85mm Male to 1.85mm Male Cable FM-P047HF Coax



### FMCA9987

#### Configuration

- Connector 1: 1.85mm Male
- Connector 2: 1.85mm Male
- Cable Type: FM-P047HF
- Coax Flex Type: Flexible

#### Features

- Max Frequency 70 GHz
- Shielding Effectivity > 90 dB
- 70% Phase Velocity
- Double Shielded
- FEP Jacket
- 500 Mating Cycles


#### Applications

- General Purpose
- Laboratory Use

#### Description

The 1.85mm male to 1.85mm male cable using FM-P047HF coax, part number FMCA9987, from Fairview Microwave is in-stock and ships same day. This Fairview 1.85mm to 1.85mm cable assembly has a male to male gender configuration with 50 ohm flexible FM-P047HF coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA9987 1.85mm male to 1.85mm male cable assembly operates to 70 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.



#### Electrical Specifications

| Description             | Minimum | Typical    | Maximum | Units        |
|-------------------------|---------|------------|---------|--------------|
| Frequency Range         | DC      |            | 70      | GHz          |
| VSWR                    |         |            | 1.4:1   |              |
| Velocity of Propagation |         | 70         |         | %            |
| RF Shielding            | 90      |            |         | dB           |
| Capacitance             |         | 29 [95.14] |         | pF/ft [pF/m] |

#### Specifications by Frequency

## 1.85mm Male to 1.85mm Male Cable FM-P047HF Coax



### FMCA9987

| Part Number | Length                   | Description           | F1   | F2    | F3    | F4    | F5    | Units | Weight (lbs) |
|-------------|--------------------------|-----------------------|------|-------|-------|-------|-------|-------|--------------|
|             |                          | Frequency             | 5000 | 10000 | 20000 | 40000 | 65000 | MHz   |              |
| FMCA9987    | Custom Lengths Available | Insertion Loss (Typ.) | 0.81 | 1.177 | 1.782 | 2.774 | 3.77  | dB/ft |              |
|             |                          |                       | 2.66 | 3.87  | 5.85  | 9.11  | 12.37 | dB/m  |              |
| FMCA9987-6  | 6 inch                   | Insertion Loss (Typ.) | 0.59 | 0.85  | 1.25  | 1.9   | 2.53  | dB    | 0.018        |
| FMCA9987-12 | 12 inch                  | Insertion Loss (Typ.) | 1.43 | 2.15  | 2.88  | 3.28  | 4.42  | dB    | 0.02         |
| FMCA9987-24 | 24 inch                  | Insertion Loss (Typ.) | 2.61 | 3.93  | 5.3   | 6.06  | 8.19  | dB    | 0.025        |
| FMCA9987-36 | 36 inch                  | Insertion Loss (Typ.) | 3.79 | 5.71  | 7.71  | 8.83  | 11.96 | dB    | 0.029        |
| FMCA9987-48 | 48 inch                  | Insertion Loss (Typ.) | 4.97 | 7.49  | 10.13 | 11.61 | 15.73 | dB    | 0.033        |

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.04 x sqrt(fGHz) dB

Loss due to Connector 2: 0.04 x sqrt(fGHz) dB

Base Weight: 0.02 pounds

Additional Weight per Inch: 0.00034 pounds

## Mechanical Specifications

### Cable Assembly

Weight 0.02 lbs [9.07 g]

### Cable

|                                      |                            |
|--------------------------------------|----------------------------|
| Cable Type                           | FM-P047HF                  |
| Impedance                            | 50 Ohms                    |
| Inner Conductor Type                 | Solid                      |
| Inner Conductor Material and Plating | Copper, Silver             |
| Dielectric Type                      | PTFE                       |
| Number of Shields                    | 2                          |
| Shield Layer 1                       | Silver Plated Copper Tape  |
| Shield Layer 2                       | Silver Plated Copper Braid |
| Jacket Material                      | FEP, Blue                  |
| Jacket Diameter                      | 0.06 in [1.52 mm]          |
| Repeated Minimum Bend Radius         | 0.1 in [2.54 mm]           |

## 1.85mm Male to 1.85mm Male Cable FM-P047HF Coax



### FMCA9987

#### Connectors

| Description                        | Connector 1                        | Connector 2                        |
|------------------------------------|------------------------------------|------------------------------------|
| Type                               | 1.85mm Male                        | 1.85mm Male                        |
| Impedance                          | 50 Ohms                            | 50 Ohms                            |
| Configuration                      | Straight                           | Straight                           |
| Mating Cycles                      | 500                                | 500                                |
| Contact Material and Plating       | Beryllium Copper, Gold over Nickel | Beryllium Copper, Gold over Nickel |
| Contact Plating Specification      | 50 µin minimum                     | 50 µin minimum                     |
| Dielectric Type                    | PEI                                | PEI                                |
| Body Material and Plating          | Beryllium Copper, Gold over Nickel | Beryllium Copper, Gold over Nickel |
| Body Plating Specification         | 50 µin minimum                     | 50 µin minimum                     |
| Coupling Nut Material and Plating  | Passivated Stainless Steel         | Passivated Stainless Steel         |
| Coupling Nut Plating Specification | ASTM-A582                          | ASTM-A582                          |
| Hex Size                           | 5/16 inch                          | 5/16 inch                          |
| Torque                             | 8 in-lbs 0.9 Nm                    | 8 in-lbs 0.9 Nm                    |
| Seal Gasket Material               | Silicone Rubber                    | Silicone Rubber                    |

#### Environmental Specifications

|                             |                                                        |
|-----------------------------|--------------------------------------------------------|
| Operating Range Temperature | -65 to +150 deg C                                      |
| Shock                       | MIL-STD-202, Method 213, Condition I                   |
| Vibration                   | MIL-STD-202, Method 204, Condition D                   |
| Thermal Shock               | MIL-STD-202, Method 107, Condition B                   |
| Salt Fog                    | MIL-STD-202, Method 101, Condition B, 5% salt solution |

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

## 1.85mm Male to 1.85mm Male Cable FM-P047HF Coax



### FMCA9987

#### Typical Performance Data

#### How to Order

Part Number Configuration:

**FMCA9987**

**- xx**

**uu**

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: FMCA9987-12 = 12 inches long cable  
FMCA9987-100cm = 100 cm long cable

1.85mm Male to 1.85mm Male Cable FM-P047HF Coax from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [1.85mm Male to 1.85mm Male Cable FM-P047HF Coax FMCA9987](#)

URL: <https://www.fairviewmicrowave.com/1.85mm-male-to-1.85mm-male-cable-fm-p047hf-coax-fmca9987-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

