

2.92mm Female (Jack) PCB Mount Connector Solder Attachment Thru Hole, .200 inches x .059 inches Hole Spacing 40GHz VSWR1.2

FMCN45915 2.92mm female PCB RF connector has a 50 Ohms impedance. Our 2.92mm female PCB connector operates at a maximum frequency of 40 GHz. Our high-quality radio frequency co-axial coaxial connector is used for general purpose test and printed circuit board applications. This 2.92mm female RF connector is stocked to be readily available for same business day shipment.

The Fairview Microwave 2.92mm female PCB connector has a VSWR of 1.2:1. This 2.92mm PCB connector has a brass body with gold plating. Our FMCN45915 connector uses a beryllium copper contact. This RF connector can operate at temperatures ranging from -40 to +165 degrees C. Additional RF connector specs and dimensions for this component can be found on its PDF specification datasheet and CAD drawings.

Fairview Microwave RF connector block has a maximum inner conductor and outer conductor resistance of 3 mOhms and 2 mOhms respectively. Our 2.92mm female RF connector with PCB termination has a 0.252 dB maximum insertion loss. The radio frequency connector is made from brass along with a contact life of 500 cycles or more. This 2.92mm connector has a beryllium copper inner contact plating. Fairview Microwave's 2.92mm jack connector has a maximum operating voltage of 250 Vrms and a dielectric withstanding voltage of 750 Vrms.

This Fairview Microwave 2.92mm female connector will ship the same business day as purchased. Our 2.92mm female connector is part of the RF, microwave, and millimeter wave components in stock for worldwide shipment. For further information on similar products, our expert technical support and trained sales team can get you the ideal RF connector as per your requirements.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		40	GHz
VSWR			1.2:1	
Insertion Loss			0.252	dB
Operating Voltage (AC)			250	Vrms
DWV (AC)			750	Vrms
Inner Cond. DC Resistance			3	mOhms
Outer Cond. DC Resistance			2	mOhms
Insulation Resistance	5,000			MOhms
RF Leakage	100			dB

Mechanical Specifications

Size	
Length	0.54 in [13.72 mm]
Width/Dia.	0.28 in [7.11 mm]
Height	0.28 in [7.11 mm]
Weight	0.115 lbs [52.16 g]
Mating Cycles	500 Cycles
Mating Torque	11.47 to 15 in-lbs [1.30 to 1.70 Nm]
Cable Retention Force	4.9 lbs [2.22 kg]



Configuration:

- 2.92mm Female Connector
- 50 Ohms
- Straight Body Geometry
- Solder Attachment

Features:

- Operating Frequency of 40 GHz Max.
- Excellent VSWR of 1.2:1
- Gold Plated Beryllium Copper Contact

Applications:

- General Purpose Test
- PCB Applications

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold
Insulation	PEI	
Outer Conductor	Brass	Gold
Body	Brass	Gold

Environmental Specifications
Temperature

Operating Range

-40 to +165 deg C

Humidity

MIL-STD-202, Method 206

Thermal Shock

MIL-STD-202, Method 107, Condition B

Salt Spray

MIL-STD-202, Method 101, Condition B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

2.92mm Female (Jack) PCB Mount Connector Solder Attachment Thru Hole, .200 inches x .059 inches Hole Spacing 40GHz VSWR1.2 from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [2.92mm Female \(Jack\) PCB Mount Connector Solder Attachment Thru Hole, .200 inches x .059 inches Hole Spacing 40GHz VSWR1.2 FMCN45915](#)

URL: <https://www.fairviewmicrowave.com/2.92mm-female-pcb-connector-fmcn45915-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

