


BMA Jack (Female) Connector Terminal Attachment 2 Hole Flange

FMCN5161



Configuration

- BMA Jack Connector
- 50 Ohms
- Straight Body Geometry
- 2 Hole Flange

Features

- Operating Frequency of 18 GHz Max.
- Excellent VSWR of 1.2:1
- Blind Mate Connector
- Gold over Nickel over Copper Plated Beryllium Copper Contact

Applications

- General Purpose Test
- Rack and Panel Mount Applications

Description

BMA Jack 2 hole Flange Mount Standard 2 hole Flange Mount Connector, part number FMCN5161, from Fairview Microwave is in-stock and ships same day. This BMA jack connector operates up to a maximum frequency of 18 GHz and offers excellent VSWR of 1.2:1. This blind mate connector is ideal for applications without direct visual or tactile access to the connection point, for example, when two circuit boards need to be mated. Fairview's FMCN5161 2 hole flange BMA connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Fairview's BMA jack 2 hole flange connector FMCN5161 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.2:1	
Insertion Loss			0.127	dB
Operating Voltage (AC)			1,000	Vrms
Dielectric Withstanding Voltage (AC)			1,500	Vrms
Inner Conductor DC Resistance			2	mOhms
Outer Conductor DC Resistance			2	mOhms
Insulation Resistance	5,000			MOhms
Impedance		50		Ohms

Mechanical Specifications

Size

Length	0.591 in [15.01 mm]
Width	0.626 in [15.9 mm]
Height	0.626 in [15.9 mm]
Weight	0.0062 lbs [2.81 g]

BMA Jack (Female) Connector Terminal Attachment 2 Hole Flange

FMCN5161



Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold over Nickel over Copper
Insulation	PTFE	
Body	Passivated Stainless Steel	

Environmental Specifications

Temperature

Operating Range

-65 to +165 deg C

Humidity

MIL-STD-202, Method 106

Thermal Shock

MIL-STD-202, Method 107, Condition B

Salt Spray

MIL-STD-202, Method 101, Condition B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

BMA Jack (Female) Connector Terminal Attachment 2 Hole Flange from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [BMA Jack \(Female\) Connector Terminal Attachment 2 Hole Flange FMCN5161](#)

URL: <https://www.fairviewmicrowave.com/product/rf-connectors/bma-jack-terminal-connector-fmcn5161.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCN5161 CAD Drawing

BMA Jack (Female) Connector Terminal Attachment 2 Hole Flange

