

## MCX Plug (Male) PCB Connector Solder Attachment Surface Mount 0.036 inch Hole Diameter



### FMCN5336

#### Configuration

- MCX Plug Connector
- 50 Ohms
- Straight Body Geometry
- Surface Mount

#### Features

- Operating Frequency of 6 GHz Max.
- Excellent VSWR of 1.2:1
- Gold over Nickel over Copper Plated Brass Contact

#### Applications

- General Purpose Test
- PCB Applications

#### Description

MCX Plug Connector Solder Attachment, part number FMCN5336, from Fairview Microwave is in-stock and ships same day. This MCX plug connector operates up to a maximum frequency of 6 GHz and offers excellent VSWR of 1.2:1.

Fairview's MCX plug surface mount connector FMCN5336 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.2:1	
Operating Voltage (AC)			250	Vrms
Dielectric Withstanding Voltage (AC)			750	Vrms
Inner Conductor DC Resistance			5	mOhms
Outer Conductor DC Resistance			2.5	mOhms
Insulation Resistance	10,000			MOhms
Impedance		50		Ohms

#### Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 1	1 to 3				GHz
Insertion Loss, Max	0.1	0.15				dB

#### Mechanical Specifications

##### Size

Length	0.232 in [5.89 mm]
Width	0.236 in [5.99 mm]
Height	0.236 in [5.99 mm]

## MCX Plug (Male) PCB Connector Solder Attachment Surface Mount 0.036 inch Hole Diameter



### FMCN5336

Weight	0.1 lbs [45.36 g]
Mating Cycles	500 Cycles
Engagement Force	5.6lbs [2.54kg]
Disengagement Force	1.8lbs [816.47g]

### Material Specifications

Description	Material	Plating
Contact	Brass	Gold over Nickel over Copper
Insulation	PTFE	
Body	Phosphor Bronze	Gold over Nickel over Copper

### Environmental Specifications

<b>Temperature</b>	
Operating Range	-55 to +155 deg C
Humidity	MIL-STD-202, Method 106
Thermal Shock	MIL-STD-202, Method 107, Condition F
Salt Spray	MIL-STD-202, Method 101, Condition B

### Compliance Certifications (see [product page](#) for current document)

### Plotted and Other Data

Notes:

MCX Plug (Male) PCB Connector Solder Attachment Surface Mount 0.036 inch Hole Diameter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [MCX Plug \(Male\) PCB Connector Solder Attachment Surface Mount 0.036 inch Hole Diameter FMCN5336](#)

URL: <https://www.fairviewmicrowave.com/product/rf-connectors/mcx-plug-pcb-connector-fmcn5336.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCN5336 CAD Drawing

MCX Plug (Male) PCB Connector Solder Attachment Surface Mount 0.036 inch Hole Diameter

