

SMA Female (Jack) Bulkhead Connector Crimp Attachment For RG174, RG188, RG316, .268 inch D Hole, IP67 Mated



FMCN5356

Configuration

- SMA Female Connector
- MIL-STD-348B
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: RG174, RG188, RG316
- Bulkhead

Features

- Operating Frequency of 11 GHz Max.
- Gold over Nickel over Copper Plated Beryllium Copper Contact
- IP67 Mated

Applications

- General Purpose Test
- Rack and Panel Mount Applications
- Custom Cable Assemblies

Description

SMA Female Bulkhead Mount Connector Crimp Attachment for RG174, RG188 and RG316 Cable IP67 Mated Mated, part number FMCN5356, from Fairview Microwave is in-stock and ships same day. This SMA female connector operates up to a maximum frequency of 11 GHz. Fairview's FMCN5356 bulkhead SMA connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications. Our FMCN5356 connector has an IP67 rating to protect against dust and temporary moisture protection under immersion conditions.

Fairview's SMA female bulkhead connector FMCN5356 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		11	GHz
VSWR		1.2:1		
Dielectric Withstanding Voltage (AC)			750	Vrms
High Potential Voltage			250	Vrms
Inner Conductor DC Resistance			3	mOhms
Outer Conductor DC Resistance			2	mOhms
Insulation Resistance	5,000			MOhms
Impedance		50		Ohms

Electrical Specification Notes:

Insertion loss is equal to $0.04 \times \sqrt{F(\text{GHz})}$ dB

Mechanical Specifications

Size

Length	0.787 in [19.99 mm]
Width	0.433 in [11 mm]
Height	0.433 in [11 mm]

SMA Female (Jack) Bulkhead Connector Crimp Attachment For RG174, RG188, RG316, .268 inch D Hole, IP67 Mated



FMCN5356

Weight	0.011 lbs [4.99 g]
Mating Cycles	100 Cycles
Mating Torque	4 to 5.3 in-lbs [[0.45 to 0.60 Nm]]
Cable Retention Force	6.1 lbs [2.77 kg]

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold over Nickel over Copper
Insulation	PTFE	
Body	Brass	Gold over Nickel over Copper
Gasket	Silicone	
Crimp Sleeve	Copper	Gold over Nickel over Copper

Environmental Specifications

Temperature	
Operating Range	-65 to +165 deg C
Ingress Protection (IP) Rating	IP67 Mated
Humidity	MIL-STD-202, Method 106
Thermal Shock	MIL-STD-202, Method 107, Condition B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Female (Jack) Bulkhead Connector Crimp Attachment For RG174, RG188, RG316, .268 inch D Hole, IP67 Mated from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [SMA Female \(Jack\) Bulkhead Connector Crimp Attachment For RG174, RG188, RG316, .268 inch D Hole, IP67 Mated FMCN5356](#)

URL: <https://www.fairviewmicrowave.com/product/rf-connectors/sma-female-rg174-rg188-rg316-connector-fmcn5356.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCN5356 CAD Drawing

SMA Female (Jack) Bulkhead Connector Crimp Attachment For RG174, RG188, RG316, .268 inch D Hole, IP67 Mated

