

2 Way Power Divider 2.4mm Interface from 18 GHz to 55 GHz Rated at 20 Watts



FMDV1265

Features

- 2-Way Power Divider
- 2.4mm Female Connectors
- 18 GHz to 55 GHz Frequency Range
- Max Power 20W (CW)
- Min Isolation 15 dB

Applications

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

Description

Fairview Microwave carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Fairview Microwave's resistive and reactive power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types. The FMDV1265 is a 2 way power divider that operates from 18 to 55 GHz and can handle up to 20 Watts (CW). This 2.4mm power divider offers 15 dB min isolation and 1.6:1 max VSWR. The package interface uses 2.4mm Female inputs on all of the ports.

Electrical Specifications

Number of Output Ports 2

Description	Min	Typ	Max	Units
Frequency Range	18		55	GHz
Impedance		50		Ohms
Input VSWR		1.5:1	1.6:1	
Output VSWR		1.5:1	1.6:1	
Insertion Loss		0.7	0.9	dB
Isolation	15	17		dB
Amplitude Balance		±0.15	±0.3	dB
Phase Balance		±4	±6	Degrees
Nominal Power Splitting		3		dB
Input Power (CW)			20	Watts
Reverse Power (CW)			0.5	Watts
Input Power (Peak)			200	Watts
10% Duty Cycle, 1 µSec PW				

Mechanical Specifications

Size	
Length	0.5 in [12.7 mm]
Width	1 in [25.4 mm]
Height	0.2 in [5.08 mm]
Weight	0.1 lbs [45.36 g]

2 Way Power Divider 2.4mm Interface from 18 GHz to 55 GHz Rated at 20 Watts



FMDV1265

Finish	Grey Paint
Housing Material and Plating	Aluminum
Configuration	
Input Connector	2.4mm Female
Output Connectors	2.4mm Female
Environmental Specifications	
Temperature	
Operating Range	-40 to +85 deg C
Storage Range	-50 to +105 deg C
Humidity	100% RH at 35°C, 95% RH at 40°C
Shock	20G for 11msec half sine wave, 3 axis both directions
Vibration	25g RMS (15 degrees) endurance, 1 hour per axis
Altitude	30,000 ft. (Epoxy Sealed controlled environment)

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data

2 Way Power Divider 2.4mm Interface from 18 GHz to 55 GHz Rated at 20 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [2 Way Power Divider 2.4mm Interface from 18 GHz to 55 GHz Rated at 20 Watts FMDV1265](#)

URL: <https://www.fairviewmicrowave.com/2-way-power-divider-2.4mm-55-ghz-fmdv1265-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMDV1265 CAD Drawing
2 Way Power Divider 2.4mm Interface from 18 GHz to 55 GHz Rated at 20 Watts

