

1.85mm Female (Jack) PCB Mount Connector,  
45 Degree angle with round contact 0.04 inches  
diameter, 67GHz VSWR1.35



## FMCN45999

### Configuration

- 1.85mm Female Connector
- 50 Ohms
- 45 Degree Body Geometry
- PCB

### Features

- Operating Frequency of 67 GHz Max.
- Good VSWR of 1.35:1
- Gold over Nickel over Copper Plated Beryllium Copper Contact

### Applications

- General Purpose Test

### Description

45° Angle 1.85mm Female PCB Mount Connector, part number FMCN45999, from Fairview Microwave is in-stock and ships same day. This 1.85mm female connector operates up to a maximum frequency of 67 GHz and offers good VSWR of 1.35:1.

Fairview's 45° Angle 1.85mm female PCB connector FMCN45999 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

### Electrical Specifications


Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		67	GHz
VSWR			1.35:1	
Insertion Loss			0.4	dB
Dielectric Withstanding Voltage (AC)			500	Vrms
Inner Conductor DC Resistance			4	mOhms
Outer Conductor DC Resistance			2.5	mOhms
Insulation Resistance	5,000			MOhms
Impedance		50		Ohms

### Mechanical Specifications

#### Size

Length	0.548 in [13.92 mm]
Width	0.276 in [7.01 mm]
Height	0.832 in [21.13 mm]
Weight	0.011 lbs [4.99 g]
Mating Cycles	500 Cycles

1.85mm Female (Jack) PCB Mount Connector,  
45 Degree angle with round contact 0.04 inches  
diameter, 67GHz VSWR1.35



**FMCN45999**

#### Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold over Nickel over Copper
Insulation	PEI	
Body	Brass	Gold over Nickel over Copper

#### Environmental Specifications

##### Temperature

Operating Range

-40 to +165 deg C

Humidity

MIL-STD-202, Method 106

Thermal Shock

MIL-STD-202, Method 107, Condition B

Salt Spray

MIL-STD-202, Method 101, Condition B

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

1.85mm Female (Jack) PCB Mount Connector, 45 Degree angle with round contact 0.04 inches diameter, 67GHz VSWR1.35 from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [1.85mm Female \(Jack\) PCB Mount Connector, 45 Degree angle with round contact 0.04 inches diameter, 67GHz VSWR1.35 FMCN45999](#)

URL: <https://www.fairviewmicrowave.com/1.85mm-female-connector-fmcn45999-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCN45999 CAD Drawing

1.85mm Female (Jack) PCB Mount Connector, 45 Degree angle with round contact 0.04 inches diameter, 67GHz VSWR1.35

