

N Female (Jack) Connector Crimp/Solder Attachment for LMR-600, LMR-600-DB, LMR-600-FR, LMR-600-UF, LMR-LW600, TCOM-600, TCOM-600-FR Cable



**FMCN5289**

**Configuration**

- N Female Connector
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: LMR-600, LMR-600-DB, LMR-600-FR, LMR-600-UF, LMR-LW600, TCOM-600, TCOM-600-FR

**Features**

- Operating Frequency of 11 GHz Max.
- Gold Plated Phosphor Bronze Contact

**Applications**

- General Purpose Test
- Custom Cable Assemblies

**Description**

Type N Female Standard Connector Crimp/Solder Attachment for LMR-600, LMR-600-DB, LMR-600-FR, LMR-600-UF, LMR-LW600, TCOM-600 and TCOM-600-FR Cable, part number FMCN5289, from Fairview Microwave is in-stock and ships same day. This type N female connector operates up to a maximum frequency of 11 GHz.

Fairview's type N female connector FMCN5289 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		11	GHz
Impedance		50		Ohms

**Mechanical Specifications**

**Size**

Length	1.95 in [49.53 mm]
Width	0.86 in [21.84 mm]
Height	0.86 in [21.84 mm]
Weight	0.127 lbs [57.61 g]

**Material Specifications**

Description	Material	Plating
Contact	Phosphor Bronze	Gold
Insulation	PTFE	
Body	Brass	Tri-Metal

**Environmental Specifications**

**Temperature**

Operating Range	-65 to +165 deg C
-----------------	-------------------

## N Female (Jack) Connector Crimp/Solder Attachment for LMR-600, LMR-600-DB, LMR-600-FR, LMR-600-UF, LMR-LW600, TCOM-600, TCOM-600-FR Cable



### FMCN5289

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

N Female (Jack) Connector Crimp/Solder Attachment for LMR-600, LMR-600-DB, LMR-600-FR, LMR-600-UF, LMR-LW600, TCOM-600, TCOM-600-FR Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [N Female \(Jack\) Connector Crimp/Solder Attachment for LMR-600, LMR-600-DB, LMR-600-FR, LMR-600-UF, LMR-LW600, TCOM-600, TCOM-600-FR Cable FMCN5289](#)

URL: <https://www.fairviewmicrowave.com/n-female-lmr-600-lmr-600-db-lmr-600-fr-lmr-600-uf-lmr-lw600-tcom-600-tcom-600-fr-connector-fmcn5289-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

# FMCN5289 CAD Drawing

N Female (Jack) Connector Crimp/Solder Attachment for LMR-600, LMR-600-DB, LMR-600-FR, LMR-600-UF, LMR-LW600, TCOM-600, TCOM-600-FR Cable

