

SMB Jack (Female) PCB Connector Thru Hole PCB  
Solder Attachment 0.2 Inches Hole Spacing



**FMCN5495**

**Configuration**

- SMB Jack Connector
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: Thru Hole PCB

**Features**

- Operating Frequency of 4 GHz Max.
- Excellent VSWR of 1.1:1
- Gold over Nickel Alloy over Copper Plated Brass Contact

**Applications**

- General Purpose Test
- PCB Applications

**Description**

SMB Jack Connector Solder Attachment for Thru hole PCB, part number FMCN5495, from Fairview Microwave is in-stock and ships same day. This SMB jack connector operates up to a maximum frequency of 4 GHz and offers excellent VSWR of 1.1:1.

Fairview's SMB jack connector FMCN5495 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.1:1	
Insertion Loss			0.2	dB
Operating Voltage (AC)			335	Vrms
Dielectric Withstanding Voltage (AC)			1,000	Vrms
Inner Conductor DC Resistance			5	mOhms
Outer Conductor DC Resistance			2.5	mOhms
Insulation Resistance	10,000			MOhms
Impedance		50		Ohms

**Mechanical Specifications**

**Size**

Length	0.47 in [11.94 mm]
Width	0.264 in [6.71 mm]
Height	0.264 in [6.71 mm]
Weight	0.003 lbs [1.36 g]
Mating Cycles	500 Cycles
Engagement Force	1.8lbs [816.47g]
Disengagement Force	1.8lbs [816.47g]

SMB Jack (Female) PCB Connector Thru Hole PCB  
Solder Attachment 0.2 Inches Hole Spacing



**FMCN5495**

**Material Specifications**

Description	Material	Plating
Contact	Brass	Gold over Nickel Alloy over Copper
Insulation	PTFE	
Body	Brass	Gold over Nickel Alloy over Copper

**Environmental Specifications**

**Temperature**

Operating Range

-65 to +165 deg C

Humidity

MIL-STD-202, Method 106

Thermal Shock

MIL-STD-202, Method 107, Condition B

Salt Spray

MIL-STD-202, Method 101, Condition B

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

SMB Jack (Female) PCB Connector Thru Hole PCB Solder Attachment 0.2 Inches Hole Spacing from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [SMB Jack \(Female\) PCB Connector Thru Hole PCB Solder Attachment 0.2 Inches Hole Spacing FMCN5495](#)

URL: <https://www.fairviewmicrowave.com/product/rf-connectors/smb-jack-thru-hole-pcb-pcb-connector-fmcn5495.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

# FMCN5495 CAD Drawing

SMB Jack (Female) PCB Connector Thru Hole PCB Solder Attachment 0.2 Inches Hole Spacing

