

**BNC Male to RA SMA Male MIL-DTL-17 Cable  
 M17/128-RG400 Coax in 12 Inch**

MIL-DTL-17 BNC (M39012/16-0014) to SMA (M39012/56-3109) cable assemblies with test reports from Fairview Microwave are part of our full line of reliable RF components available with same-day shipping. These COTS (commercial-off-the-shelf) cable assemblies using M17/128-RG400 have traceable processes and materials that are recorded and provided in the included test report. The MIL-DTL-17 coaxial cable and MIL-PRF-39012 connectors are assembled with J-STD-001 soldering processes and meet WHMA-A-620 workmanship criteria. These carefully selected materials, assembly processes and test sequence ensure a dependable cable assembly for high reliability applications where the cost of failure or replacement is high. Each serialized BNC to SMA MIL-DTL-17 cable assembly is traceable to its component lots and test data ship with every cable.

This MIL-C-17 M39012/16-0014 to M39012/56-3109 cable assembly using M17/128-RG400 datasheet PDF contains specifications, CAD drawing and dimensions that are shown below. Fairview Microwave offers these high reliability RF cable assemblies with test data, and many other RF, microwave and millimeter wave components which allow designers to configure and customize their signal systems however they like. Whether the need is to provide reliable MIL-DTL-17 interconnects or supporting test reports, Fairview Microwave has the right cable assemblies for the job. Fairview can also expertly build your custom cable assemblies for you and ship same day.

**Referenced Specifications**

|                |   |
|----------------|---|
| IPC/WHMA-A-620 | Requirements and Acceptance for Cable and Wire Harness Assemblies   |
| MIL-DTL-17     | Cables, Radio Frequency, Flexible and Semirigid, General Specification for  |
| MIL-STD-348    | Radio Frequency Connector Interfaces for MIL-DTL-3643, MIL-DTL-3650, MIL-DTL-3655, MIL-DTL-25516, MIL-PRF-31031, MIL-PRF-39012, MIL-PRF-49142, MIL-PRF... |
| MIL-PRF-39012  | Connectors, Coaxial, Radio Frequency, General Specification for   |
| IPC J-STD-001  | Requirements for Soldered Electrical and Electronic Assemblies  |
| IPC J-STD-006  | Requirements for Electronic Grade Solder Alloys and Fluxed and Non-Fluxed Solid Solders for Electronic Soldering Applications                             |
| SAE AS5942     | Marking of Electrical Insulating Materials  |
| SAE AS23053    | Insulation Sleeving, Electrical, Heat Shrinkable, General Specifications For  |
| SAE AS22520    | Crimping Tools, Wire Termination, General Specification For   |

**Material Specifications**

| Component     | Specification                                   |
|---------------|---|
| Cable         | M17/128-RG400 in accordance with MIL-DTL-17     |
| Connector 1   | M39012/16-0014 in accordance with MIL-PRF-39012 |
| Connector 2   | M39012/56-3109 in accordance with MIL-PRF-39012 |
| Heat Shrink 1 | M23053/5-106-0 in accordance with SAE AS23053   |
| Heat Shrink 2 | M23053/5-106-0 in accordance with SAE AS23053   |



**Configuration:**

- Connector 1: M39012/16-0014(BNC Male)
- Connector 2: M39012/56-3109(SMA Male Right Angle)
- Cable: M17/128-RG400

**Features:**

- Max Frequency 4 GHz
- 69.5% Phase Velocity
- Double Shielded
- J-STD-Soldering
- Lot Traceability Data
- Qualified cable and connectors (QPL)
- Acceptance Test Report
- RF Test Data
- In stock and ready to ship

**Applications:**

- Hi-Reliability
- Unmanned Systems
- Drones
- MIL-DTL-17 Requirements
- Military Electronics

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

Solder

SN63 in accordance with J-STD-006

### Electrical Specifications

| Description                          | Min         | Typ  | Max   | Units           |
|--------------------------------------|-------------|------|-------|-----------------|
| Frequency Range                      | DC          |      | 4     | GHz             |
| VSWR                                 |             |      | 1.6:1 |                 |
| Velocity of Propagation              |             | 69.5 |       | %               |
| Capacitance                          | 32 [104.99] |      |       | pF/ft [pF/m]    |
| DC Resistance Inner Conductor        | 0.91 [2.99] |      |       | Ω/1000ft [Ω/Km] |
| Dielectric Withstanding Voltage (AC) |             |      | 1,000 | Vrms            |

### Specifications by Frequency

| Description           | F1  | F2  | F3   | F4   | F5   | Units |
|-----------------------|-----|-----|------|------|------|-------|
| Frequency             | 0.1 | 0.4 | 1    | 3    | 4    | GHz   |
| Insertion Loss (Max.) | 0.2 | 0.3 | 0.42 | 0.74 | 0.84 | dB    |

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable used in this assembly. The Insertion Loss includes an estimated insertion loss of  $0.15 \cdot \sqrt{\text{GHz}}$  dB maximum for the SMA Male right angle connector and 0.1 dB for the BNC Male connector.

### Mechanical Specifications

#### Cable Assembly

| Description          | Min        | Typ        | Max          | Units   |
|----------------------|------------|------------|--------------|---------|
| Length*              | 12 [304.8] | 12 [304.8] | 12.5 [317.5] | in [mm] |
| Cable Outer Diameter | 0.19       | 0.195      | 0.2          | in      |
| Weight               |            |            | 0.13 [58.97] | lbs [g] |

#### Cable Characteristics

| Component                    | Specification             |
|------------------------------|---------------------------|
| Cable Type                   | M17/128-RG400             |
| Impedance                    | 50 Ohms                   |
| Inner Conductor Type         | Stranded                  |
| Inner Conductor Mat. & Plat. | Copper Clad Steel, Silver |
| Dielectric Type              | PTFE                      |
| Number of Shields            | 2                         |
| Shield Layer 1               | Silver Clad Copper        |
| Shield Layer 2               | Silver Clad Copper        |
| Outer Conductor Diameter     | 0.171 in [4.34 mm]        |

**Connector Characteristics**

| Description                | Connector 1       | Connector 2          |
|----------------------------|-------------------|----------------------|
| Type                       | BNC Male          | SMA Male Right Angle |
| Specification              | MIL-PRF-39012     | MIL-PRF-39012        |
| Impedance                  | 50 Ohms           | 50 Ohms              |
| Contact Mat. & Plat.       | Brass, Gold       | Brass, Gold          |
| Contact Plating Spec.      | MIL-G-45204       | ASTM B488            |
| Dielectric Type            | Teflon            | Teflon               |
| Body Mat. & Plat.          | Brass, Silver     | Steel, Gold          |
| Body Plating Spec.         | QQ-S-365          | ASTM B488            |
| Coupling Nut Mat. & Plat.  |                   | Steel, Passivated    |
| Coupling Nut Plating Spec. |                   | AMS-QQ-P-35          |
| Seal Gasket Material       | Silicone Rubber   | Silicone Rubber      |
| Contact Gage Spec.         | 0.210 to 0.230 in | 0.000 in min         |
| Insulator Gage Spec.       | 0.208 to 0.228 in | 0.000 inmin          |

Mechanical Specification Notes:

**Environmental Specifications**

| Description                 | Specification     |
|-----------------------------|-------------------|
| Temperature Operating Range | -55 to +165 deg C |

**Compliance Certifications** (see [product page](#) for current document)

**Process Specifications**

| Process     | Specification                                       |
|-------------|---|
| Soldering   | in accordance with J-STD-001, class 3               |
| Crimping    | dies in accordance with SAE AS22520                 |
| Marking     | shall meet the adherence requirements of SAE AS5942 |
| Workmanship | shall be in accordance with IPC/WHMA-A-620, class 3 |

**Tests and Inspections**

| Test  | Sampling     |
|---|--------------|
| Connector Gaging (pin and insulator position)   | 100%         |
| Insertion Loss                                  | 100%         |
| VSWR  | 100%         |
| Dielectric Withstanding Voltage (DWV)           | 100%         |
| Visual - workmanship, configuration and marking | 100%         |
| Length  | C=0, 1.5 AQL |
| Mass  | C=0, 1.5 AQL |

**Plotted and Other Data**

Notes:

- Values at 25°C, sea level.

**How to Order**

Part Number Configuration:

**FMHR0062 - xx uu**



Example: FMHR0062-12 = 12 inches long cable  
 FMHR0062-100cm = 100 cm long cable

Cable Assembly Length Tolerances:

| Imperial English    |                 | Metric              |                  |
|---------------------|-----------------|---------------------|------------------|
| "L" ≤ 1 ft          | +0.5 in / -0 in | "L" ≤ 0.3 m         | +12.5 mm / -0 mm |
| 1 ft < "L" ≤ 5 ft   | +1 in / -0 in   | 0.3 m < "L" ≤ 1.5 m | +25 mm / -0 mm   |
| 5 ft < "L" ≤ 10 ft  | +2 in / -0 in   | 1.5 m < "L" ≤ 3 m   | +50 mm / -0 mm   |
| 10 ft < "L" ≤ 25 ft | +3 in / -0 in   | 3 m < "L" ≤ 7.5 m   | +75 mm / -0 mm   |
| 25 ft < "L"         | +2%"L" / -0%"L" | 7.5 m < "L"         | +2%"L" / -0%"L"  |


\* Cable Length = "L"

BNC Male to RA SMA Male MIL-DTL-17 Cable M17/128-RG400 Coax in 12 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [BNC Male to RA SMA Male MIL-DTL-17 Cable M17/128-RG400 Coax in 12 Inch FMHR0062-12](https://www.fairviewmicrowave.com/bnc-male-ra-sma-male-cable-m17-128-rg400-coax-fmhr0062-12-p.aspx)

URL: <https://www.fairviewmicrowave.com/bnc-male-ra-sma-male-cable-m17-128-rg400-coax-fmhr0062-12-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



**STANDARD TOLERANCES**

.X ±0.2  
 .XX ±0.01  
 .XXX ±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

**NOTES:**

1. BLACK HEAT SHRINK WITH WHITE MARKINGS 3 PLACES.

|   |              |   |        |                           |
|---|--------------|---|--------|---------------------------|
|   |              | NOTES:<br>1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.<br>2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.<br>3. DIMENSIONS ARE IN INCHES [mm]. |        |                           |
| <b>TITLE</b><br>BNC Male to RA SMA Male MIL-DTL-17 Cable<br>M17/128-RG400 Coax in 12 Inch |              | <b>DWG NO</b><br>FMHR0062   |        | <b>CAGE CODE</b><br>3FKR5 |
| CAD FILE 11/16/18   | SHEET 1 OF 1 | SCALE N/A   | SIZE A | CN2379                    |