

RA SMA Male to SMA Female Bulkhead MIL-DTL-17 Cable M17/119-RG174 Coax in 18 Inch

MIL-DTL-17 SMA (M39012/56-3107) to SMA (M39012/59-3026) cable assemblies with test reports from Fairview Microwave are part of our full line of reliable RF components available with same-day shipping. These COTS (commercial-off-the-shelf) cable assemblies using M17/119-RG174 have traceable processes and materials that are recorded and provided in the included test report. The MIL-DTL-17 coaxial cable and MIL-PRF-39012 connectors are assembled with J-STD-001 soldering processes and meet WHMA-A-620 workmanship criteria. These carefully selected materials, assembly processes and test sequence ensure a dependable cable assembly for high reliability applications where the cost of failure or replacement is high. Each serialized SMA to SMA MIL-DTL-17 cable assembly is traceable to its component lots and test data ship with every cable.

This MIL-C-17 M39012/56-3107 to M39012/59-3026 cable assembly using M17/119-RG174 datasheet PDF contains specifications, CAD drawing and dimensions that are shown below. Fairview Microwave offers these high reliability RF cable assemblies with test data, and many other RF, microwave and millimeter wave components which allow designers to configure and customize their signal systems however they like. Whether the need is to provide reliable MIL-DTL-17 interconnects or supporting test reports, Fairview Microwave has the right cable assemblies for the job. Fairview can also expertly build your custom cable assemblies for you and ship same day.

Referenced Specifications

| | |
|----------------|---|
| IPC/WHMA-A-620 | Requirements and Acceptance for Cable and Wire Harness Assemblies |
| MIL-DTL-17 | Cables, Radio Frequency, Flexible and Semirigid, General Specification for |
| MIL-STD-348 | Radio Frequency Connector Interfaces for MIL-DTL-3643, MIL-DTL-3650, MIL-DTL-3655, MIL-DTL-25516, MIL-PRF-31031, MIL-PRF-39012, MIL-PRF-49142, MIL-PRF... |
| MIL-PRF-39012 | Connectors, Coaxial, Radio Frequency, General Specification for |
| IPC J-STD-001 | Requirements for Soldered Electrical and Electronic Assemblies |
| IPC J-STD-006 | Requirements for Electronic Grade Solder Alloys and Fluxed and Non-Fluxed Solid Solders for Electronic Soldering Applications |
| SAE AS5942 | Marking of Electrical Insulating Materials |
| SAE AS23053 | Insulation Sleeving, Electrical, Heat Shrinkable, General Specifications For |
| SAE AS22520 | Crimping Tools, Wire Termination, General Specification For |

Material Specifications

| Component | Specification |
|---------------|---|
| Cable | M17/119-RG174 in accordance with MIL-DTL-17 |
| Connector 1 | M39012/56-3107 in accordance with MIL-PRF-39012 |
| Connector 2 | M39012/59-3026 in accordance with MIL-PRF-39012 |
| Heat Shrink 1 | M23053/5-105-0 in accordance with SAE AS23053 |
| Heat Shrink 2 | M23053/5-104-0 in accordance with SAE AS23053 |



Configuration:

- Connector 1: M39012/56-3107(SMA Male Right Angle)
- Connector 2: M39012/59-3026(SMA Female Bulkhead)
- Cable: M17/119-RG174

Features:

- Max Frequency 1 GHz
- 65.9% Phase Velocity
- PVC Jacket
- J-STD-Soldering
- Lot Traceability Data
- Qualified cable and connectors (QPL)
- Acceptance Test Report
- RF Test Data
- In stock and ready to ship

Applications:

- Hi-Reliability
- Unmanned Systems
- Drones
- MIL-DTL-17 Requirements
- Military Electronics

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Solder

SN63 in accordance with J-STD-006

Electrical Specifications

| Description | Min | Typ | Max | Units |
|--------------------------------------|---------------|------|-------|---------------------------------|
| Frequency Range | DC | | 1,000 | MHz |
| VSWR | | | 1.5:1 | |
| Velocity of Propagation | | 65.9 | | % |
| Capacitance | 32.2 [105.64] | | | pF/ft [pF/m] |
| DC Resistance Inner Conductor | 0.97 [3.18] | | | $\Omega/1000ft$ [Ω/Km] |
| Dielectric Withstanding Voltage (AC) | | | 750 | Vrms |

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|------|------|-------|----|-------|
| Frequency | 50 | 100 | 400 | 1,000 | | MHz |
| Insertion Loss (Max.) | 0.15 | 0.22 | 0.51 | 0.89 | | dB |

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable used in this assembly. The Insertion Loss includes an estimated insertion loss of $0.06 \cdot \sqrt{\text{GHz}}$ dB for the SMA Female connector and $0.15 \cdot \sqrt{\text{GHz}}$ dB for the SMA Male right angle connector.

Mechanical Specifications

Cable Assembly

| Description | Min | Typ | Max | Units |
|----------------------|------------|------------|--------------|---------|
| Length* | 18 [457.2] | 18 [457.2] | 19 [482.6] | in [mm] |
| Cable Outer Diameter | 0.105 | 0.11 | 0.115 | in |
| Weight | | | 0.07 [31.75] | lbs [g] |

Cable Characteristics

| Component | Specification |
|------------------------------|--------------------|
| Cable Type | M17/119-RG174 |
| Impedance | 50 Ohms |
| Inner Conductor Type | Stranded |
| Inner Conductor Mat. & Plat. | Copper Clad Steel |
| Dielectric Type | PE |
| Number of Shields | 1 |
| Shield Layer 1 | Tinned Copper |
| Outer Conductor Diameter | 0.088 in [2.24 mm] |
| Jacket Material | PVC |

Connector Characteristics

| Description | Connector 1 | Connector 2 |
|-------------------------------|----------------------|------------------------|
| Type | SMA Male Right Angle | SMA Female Bulkhead |
| Specification | MIL-PRF-39012 | MIL-PRF-39012 |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Mat. & Plat. | Brass, Gold | Beryllium Copper, Gold |
| Contact Plating Spec. | ASTM B488 | ASTM B488 |
| Dielectric Type | Teflon | Teflon |
| Outer Conductor Mat. & Plat. | | Steel, Passivated |
| Outer Conductor Plating Spec. | | QQ-P-35 |
| Body Mat. & Plat. | Steel, Gold | Steel, Passivated |
| Body Plating Spec. | ASTM B488 | QQ-P-35 |
| Coupling Nut Mat. & Plat. | Steel, Passivated | Steel, Passivated |
| Coupling Nut Plating Spec. | AMS-QQ-P-35 | QQ-P-35 |
| Seal Gasket Material | Silicone Rubber | Silicone Rubber |
| Contact Gage Spec. | 0.000 in min | 0.000 to 0.010 in |
| Insulator Gage Spec. | 0.000 in min | 0.000 inmin |

Mechanical Specification Notes:

Environmental Specifications

| Description | Specification |
|-----------------------------|------------------|
| Temperature Operating Range | -40 to +85 deg C |

Compliance Certifications (see [product page](#) for current document)

Process Specifications

| Process | Specification |
|-------------|---|
| Soldering | in accordance with J-STD-001, class 3 |
| Crimping | dies in accordance with SAE AS22520 |
| Marking | shall meet the adherence requirements of SAE AS5942 |
| Workmanship | shall be in accordance with IPC/WHMA-A-620, class 3 |

Tests and Inspections

| Test | Sampling |
|---|--------------|
| Connector Gaging (pin and insulator position) | 100% |
| Insertion Loss | 100% |
| VSWR | 100% |
| Dielectric Withstanding Voltage (DWV) | 100% |
| Visual - workmanship, configuration and marking | 100% |
| Length | C=0, 1.5 AQL |
| Mass | C=0, 1.5 AQL |

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

How to Order

Part Number Configuration:

FMHR0109 - xx uu



Example: FMHR0109-12 = 12 inches long cable
 FMHR0109-100cm = 100 cm long cable

Cable Assembly Length Tolerances:

| Imperial English | | Metric | |
|---------------------|-----------------|---------------------|------------------|
| "L" ≤ 1 ft | +0.5 in / -0 in | "L" ≤ 0.3 m | +12.5 mm / -0 mm |
| 1 ft < "L" ≤ 5 ft | +1 in / -0 in | 0.3 m < "L" ≤ 1.5 m | +25 mm / -0 mm |
| 5 ft < "L" ≤ 10 ft | +2 in / -0 in | 1.5 m < "L" ≤ 3 m | +50 mm / -0 mm |
| 10 ft < "L" ≤ 25 ft | +3 in / -0 in | 3 m < "L" ≤ 7.5 m | +75 mm / -0 mm |
| 25 ft < "L" | +2%"L" / -0%"L" | 7.5 m < "L" | +2%"L" / -0%"L" |


* Cable Length = "L"

RA SMA Male to SMA Female Bulkhead MIL-DTL-17 Cable M17/119-RG174 Coax in 18 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [RA SMA Male to SMA Female Bulkhead MIL-DTL-17 Cable M17/119-RG174 Coax in 18 Inch FMHR0109-18](https://www.fairviewmicrowave.com/ra-sma-male-sma-female-cable-m17-119-rg174-coax-fmhr0109-18)

URL: <https://www.fairviewmicrowave.com/ra-sma-male-sma-female-cable-m17-119-rg174-coax-fmhr0109-18-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



| STANDARD TOLERANCES | |
|---------------------|--------|
| .X | ±0.2 |
| .XX | ±0.01 |
| .XXX | ±0.005 |

- NOTES:
 1. BLACK HEAT SHRINK WITH WHITE MARKINGS 3 PLACES.

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

| | | | | |
|---|---|---------------------------|---------------------------|--------|
| <p>Fairview Microwave RF COMPONENTS ON DEMAND. <i>Done!</i></p> | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | |
| | TITLE RA SMA Male to SMA Female Bulkhead MIL-DTL-17 Cable M17/119-RG174 Coax in 18 Inch | DWG NO FMHR0109 | CAGE CODE 3FKR5 | |
| CAD FILE 11/16/18 | SHEET 1 OF 1 | SCALE N/A | SIZE A | CN2379 |