

SMA Schottky Diode Zero Bias Detector, 500 MHz to 18 GHz, +20 dBm Max Pin, Positive Video Out, MIL-STD-202, Square



FMMT6032

Features

- Zero bias Schottky diode detector
- Broadband frequency range: 0.5 GHz to 18.0 GHz
- Positive video output polarity
- Sensitivity: 500 $\pm$ 50 mV/mW typical
- Frequency flatness: $\pm$ 3.5 dB max
- Low VSWR: 2.0:1
- Maximum input power: +20 dBm
- SMA male RF input and SMA female video output connectors
- Operating temperature range: -54 °C to +100 °C
- Environmentally tested to MIL-STD-202 (humidity, shock, vibration, altitude, temperature cycle)

Applications

- RF power and level monitoring
- Broadband test and measurement equipment/Transmitter monitoring and leveling
- Radar and surveillance systems
- Electronic warfare (EW) and ECM receivers
- detector front-ends for receiver chains
- General-purpose RF measurement applications
- Military and aerospace systems

Description

This coaxial packaged Zero Bias Schottky Diode Detector operates over a broadband frequency range of 0.5 GHz to 18.0 GHz and is designed for accurate RF signal detection in CW and broadband measurement applications. The zero-bias Schottky design provides reliable detection without the need for external biasing, making it ideal for compact and simplified system designs. The detector delivers a stable positive polarity video output with a typical sensitivity of 500 $\pm$ 50 mV/mW, dependent on input power and frequency. With good frequency flatness and low VSWR, this detector supports consistent performance across a wide frequency band. The rugged SMA-connectorized package is environmentally qualified to MIL-STD-202, ensuring dependable operation in harsh military, aerospace, and laboratory environments. Maximum input power handling is +20 dBm.

Electrical Specifications (@ +25°C)

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.5		18	GHz
VSWR		1.5:1	2:1	
Voltage Sensitivity		500		mV/mW
Flatness			$\pm$ 3.5	dB
Input Power			+20	dBm CW
Video Capacitance		30		pF
Operating Temperature Range	-54		+100	deg C
Output Polarity		Positive		

Electrical Specification Notes:

Mechanical Specifications

Size

Length	1.38 in	[35.05 mm]
Width	0.5 in	[12.7 mm]
Height	0.23 in	[5.84 mm]
Weight	0.03 lbs	[13.61 g]
Connector 1	SMA Male	

SMA Schottky Diode Zero Bias Detector, 500 MHz to 18 GHz,
+20 dBm Max Pin, Positive Video Out, MIL-STD-202, Square



FMMT6032

Connector 2

SMA Female

Configuration

Mechanical Specification Notes:

Environmental Specifications

Temperature

Operating Temperature

-54 to +100 deg C

Storage Temperature

-65 to +125 deg C

Temperature Cycling

MIL-STD-202, Method 107D Cond. A

Humidity

MIL-STD-202, Method 103B Cond. B

Shock

MIL-STD-202, Method 213B Cond. B

Vibration

MIL-STD-202, Method 204D Cond. B

Altitude

MIL-STD-202, Method 105C Cond. B

Environmental Specification Notes:

Compliance Certifications

Plotted and Other Data

Notes:

SMA Schottky Diode Zero Bias Detector, 500 MHz to 18 GHz, +20 dBm Max Pin, Positive Video Out, MIL-STD-202, Square from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.



For additional information on this product, please click the following link: [SMA Schottky Diode Zero Bias Detector, 500 MHz to 18 GHz, +20 dBm Max Pin, Positive Video Out, MIL-STD-202, Square FMMT6032](#)

URL: <https://www.fairviewmicrowave.com/schottky-diode-zero-bias-detector-sma-male-500-mhz-18-ghz-fmmt6032>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

SMA Schottky Diode Zero Bias Detector, 500 MHz to 18 GHz, +20 dBm
Max Pin, Positive Video Out, MIL-STD-202, Square

REVISION	
ZONE	REV
A	INITIAL RELEASE
01/29/2026	CHANGED BY
KDANG	APPROVED
JNAJERA	



SMA MALE SMA FEMALE

UNLESS OTHERWISE SPECIFIED, ALL LEADING DIMENSIONS ARE IN INCHES. DIMENSIONS IN [] ARE MILLIMETERS. TOLERANCES: X = ± 2.5 [0.5] XX = ± 0.2 [0.5] XXX = ± 0.05 [0.13] FRACTIONS ANGLES ± 1° CABLE LENGTH TOLERANCES: ≤ 12 [305] = ± 0.125 [3.175] > 12 [305] ≤ 60 [1524] = ± 0.15 [3.81] > 60 [1524] ≤ 120 [3048] = ± 0.20 [5.08] > 120 [3048] ≤ 300 [7620] = ± 0.25 [6.35] > 300 [7620] = ± 0.375 [9.53] ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE. UNDIMENSIONED SIZE AND LOCATION MAY VARY. DIMENSIONED COLORS MAY VARY.		Fairview Microwave® an INFINIT® brand Website: www.FairviewMicrowave.com Phone: 1.800.771.5.4396 1.972.649.6678		 INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	SCALE SHEET 1 OF 1	
DESCRIPTION SMA SCHOTTKY DIODE ZERO BIAS DETECTOR, 500 MHZ TO 18 GHZ, ± 20 dBm MAX PIN, POSITIVE VIDEO OUT, MIL-STD-202, SQUARE		SIZE A	CAGE CODE 3FKR5	DRAWN BY KDANG	ITEM NO. FMMT6032	REV A

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.