

## SPDT Latching DC to 18 GHz Terminated Electro-Mechanical Relay Switch, Indicators, TTL, up to 90W, 28V, SMA

The FMSW6407 is a Single Pole Double Throw (SPDT) electromechanical relay switch that operates across a wide frequency range of DC to 18 GHz and can handle up to 90 Watts of CW input power in a break before make condition. The design features a Latching actuator and is rated for 5M life cycles for high reliability operation. Impressive performance includes insertion loss less than 0.15 dB typical and isolation greater than 85 dB typical. The Latching TTL controlled actuator includes Indicators and 5 Watt Internal Terminations with a +28 Vdc bias voltage, and operates over a temperature range of -25°C to +70°C. The rugged and compact package assembly supports SMA Female connectors and Solder Pins for DC Control. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for shock and random vibration.

### Electrical Specifications

Switch Type	SPDT, Terminated
Actuator Type	Latching
Switching Sequence	Break before Make
Actuator Options	Indicators, TTL Logic
TTL Control	on: 2.4 to 5 Volts off: 0 to 0.8 Volts
Indicator Rating	1 Watts / 32 Volts / 125 mA

Description	Min	Typ	Max	Units
Frequency Range	DC		18	GHz
Impedance		50		Ohms
Termination Impedance		50		Ohms
Operating Voltage	26	28	30	Volts
Actuating Current @ 28 Volts		90		mA
VSWR		1.2:1	1.4:1	
Insertion Loss		0.15	0.35	dB
Insertion Loss Repeatability				
Isolation	65	85		dB
Input Power (CW)			60	Watts
Termination Input Power (CW)			5	Watts
Switching Time			20	ms

### Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC - 6	6 - 12	12 - 18			GHz
VSWR, Max	1.2:1	1.3:1	1.4:1			
Insertion Loss, Max	0.15	0.25	0.35			dB
Isolation, Min	85	70	65			dB
Power In, Typ (CW)	90	75	60			Watts



### Features:

- Single Pole Double Throw
- DC to 18 GHz Frequency Range
- Isolation greater than 85 dB typical
- 5M Cycle Min Operating Life
- +28 Volt DC
- 90 Watt average Power
- Latching Actuator
- 1 Watt Indicators
- TTL Control
- Internally Terminated
- -25 to +70°C Operating Temperature
- Insertion Loss as low as 0.15 dB Max
- VSWR as low as 1.2:1 max
- SMA Female RF connectors
- Solder Pins for DC Control
- Hot Switching Capability - Consult Factory
- S-Parameter Data available upon request

### Applications:

- High Performance Relay Switch
- Military Communications
- Communications Systems
- Test & Measurement

Fairview Microwave  
1130 Junction Dr. #100  
Allen, TX 75013  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Mechanical Specifications

### Size

Weight	0.165 lbs [74.84 g]
Package Type	Connectorized
Operating Life	5,000,000 Cycles

### Connectors

RF Connector Type	SMA Female
Control Connector	Solder Pin

## Environmental Specifications

### Temperature

Operating Range	-25 to +70 deg C
Storage Range	-55 to +100 deg C


Shock	MIL-STD-202 Method 213, Cond. D 500G Non Operating
Vibration	MIL-STD-202 Method 214, Cond. D 10G RMS Non Operating


## Compliance Certifications (see [product page](#) for current document)

## Plotted and Other Data

Notes:

### Typical Performance Data







SPDT Latching DC to 18 GHz Terminated Electro-Mechanical Relay Switch, Indicators, TTL, up to 90W, 28V, SMA from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: [SPDT Latching DC to 18 GHz Terminated Electro-Mechanical Relay Switch, Indicators, TTL, up to 90W, 28V, SMA FMSW6407](https://www.fairviewmicrowave.com/spdt-latching-18-ghz-terminated-electro-mechanical-relay-switch-60w-28v-sma-fmsw6407)

URL: <https://www.fairviewmicrowave.com/spdt-latching-18-ghz-terminated-electro-mechanical-relay-switch-60w-28v-sma-fmsw6407-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



7X SOLDER TERMINALS  
SOLDER WIRE USING SN96,  
MAXIMUM TEMP 430°F FOR  
NO MORE THAN 5 SEC.



**STANDARD TOLERANCES**

.X ±0.2  
.XX ±0.01  
.XXX ±0.005

\*STANDARD TOLERANCES APPLY  
ONLY TO DIMENSIONS IN INCHES

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

**NOTES:**

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

**TITLE**

SPDT Latching DC to 18 GHz Terminated Electro-Mechanical Relay Switch, Indicators, TTL, up to 90W, 28V, SMA

**DWG NO**

FMSW6407

**CAGE CODE**

3FKR5


CAD FILE 090617

SHEET 1 OF 2

SCALE N/A

SIZE A

7361



SCHEMATIC SHOWN IN LATCHING POSITON

OPERATIONAL							
LOGIC TABLE							
TERMINALS		RF PORTS		INDICATOR		TERMINATION	
1	2	J1-JC	J2-JC	B-C	A-C	J2 TERMINATED	J1 TERMINATED
0	0	NO CHANGE		NO CHANGE		NO CHANGE	
0	1	OFF	ON	OFF	ON	OFF	ON
1	0	ON	OFF	ON	OFF	ON	OFF
1	1	FORBIDDEN		FORBIDDEN		FORBIDDEN	

STANDARD TOLERANCES

.X ±0.2  
.XX ±0.01  
.XXX ±0.005

\*STANDARD TOLERANCES APPLY  
ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SPDT Latching DC to 18 GHz Terminated Electro-Mechanical Relay Switch, Indicators, TTL, up to 90W, 28V, SMA

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].

DWG NO

FMSW6407

CAGE CODE

3FKR5

CAD FILE 090617

SHEET 2 OF 2

SCALE N/A

SIZE A

7361