

SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm

The FMSW7288 is a Single Pole Four Throw (SP4T) electromechanical relay switch that operates across an ultra wide frequency range from DC to 43 GHz and can handle up to 10 Watts of Average Power in a break before make condition. The 50 Ohm design is rated for 2 million lifecycles and features a Normally Open Actuator where the selected position remains active with constant voltage, all positions are open when voltage is removed. Impressive typical performance includes 0.6 dB insertion loss and isolation greater than 70 dB. This switch requires +12 Vdc bias voltage and operates over a temperature range of -25°C to +65°C. The rugged and compact package assembly supports 2.92mm female connectors and solder terminal pins for DC control. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for shock and random vibration.

Electrical Specifications (TA = +25°C, DC Voltage = 12 Vdc)

Switch Type	SP4T
Actuator Type	Normally Open

Description	Min	Typ	Max	Units
Frequency Range	DC		43	GHz
Operating Voltage	11	12	13	Volts
Actuating Current @ 12 Volts			400	mA
VSWR		1.4:1	2.1:1	
Insertion Loss		0.6	1.6	dB
Isolation	40	85		dB
Input Power			10	Watts
Switching Time			20	ms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC - 6	6 - 12	12 - 18	18 - 28	28 - 34	GHz
VSWR, Max	1.25:1	1.4:1	1.5:1	1.8:1	1.8:1	
Insertion Loss, Max	0.2	0.4	0.5	0.9	1	dB
Isolation, Min	70	60	60	60	60	dB

Performance by Frequency

Description	F6	F7	F8	F9	F10	Units
Frequency Range	34 - 40	40 - 43				GHz
VSWR, Max	1.8:1	2.1:1				
Insertion Loss, Max	1.3	1.6				dB
Isolation, Min	50	40				dB



Features:

- Single Pole Four Throw (SP4T) Electromechanical Relay Switch
- DC to 43 GHz Frequency Range
- Normally Open Actuator
- 2M Lifecycle Rating
- Insertion Loss 0.6 dB typ
- Isolation > 70 dB typ
- VSWR as low as 1.25:1 max
- Solder Terminal Pins for DC Control
- +12 Volt DC Bias
- 2.92mm Female Connectors
- -25°C to +65°C Operating Temperature
- Up to 10 Watts Average Power Handling
- 50 Ohm Design
- Hot Switching Capability - Consult Factory
- S-Parameter Data available upon request
- Rugged Design meets Mil-STD-202 Test Conditions

Applications:

- Aerospace & Defense
- Test & Measurement
- Microwave Radio Systems
- Military & Commercial Communication Systems
- Research & Development
- SATCOM
- Wireless Communications
- Enterprise
- IoT

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Mechanical Specifications

Size

Length	1.75 in [44.45 mm]
Width/Diameter	1.75 in [44.45 mm]
Height	1.75 in [44.45 mm]
Weight	0.22 lbs [99.79 g]
Body Material and Plating	Electroless Nickel

Connectors

RF Connector Type	2.92mm Female
Control Connector	Solder Terminals

Environmental Specifications

Temperature

Operating Range	-25 to +65 deg C
Storage Range	-55 to +100 deg C


Shock	MIL-STD-202 Method 213, Condition D, 500G (non operational)
Vibration	MIL-STD-202 Method 204, Condition D, 10G RMS (non operational)


Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data


Notes:

Typical Performance Data





Power Handling vs. Frequency




SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [SP4T, Electromechanical Relay Normally Open Switch, DC to 43 GHz, 12VDC, 10W, Solder Terminals, 2.92mm FMSW7288](https://www.fairviewmicrowave.com/sp4t-normally-open-43-ghz-electro-mechanical-relay-switch-12v-2.92mm-fmsw7288-p.aspx)

URL: <https://www.fairviewmicrowave.com/sp4t-normally-open-43-ghz-electro-mechanical-relay-switch-12v-2.92mm-fmsw7288-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





RF POSITION SCHEMATIC

SP4T, Electromechanical Relay Normally Open Switch,
DC to 43 GHz, 12VDC, 10W, Solder Terminals,
2.92mm

TERMINALS	REF PATH			
	J1	J2	J3	J4
PIN ASSIGNMENT	1	ON	OFF	OFF
	2	OFF	ON	OFF
	3	OFF	OFF	ON
	4	OFF	OFF	ON

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN MILLIMETERS			INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5
$X = \pm .2$ FRACTIONS $.XX = \pm .02$ [.5] $\pm 1/32$ $.XXX = \pm .005$ [.13] ANGLES $\pm 1^\circ$	Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.972.649.6678	SCALE	2 OF 2
DESCRIPTION	SP4T, NO. 43GHz, 12VDC, 2.92mm, solder terminal	NONE	SHEET
SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	3FKR5	BPUCHASKI	FMSW7288
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.	REV	A	

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.