

**75 Ohm N Male to 75 Ohm F Female Cable 75 Ohm
 FM-SF200LL75 Coax in 100 cm**

The broadband 75 ohm type N male to 75 ohm type F female 100 cm cable using 75 ohm FM-SF200LL75 coax, part number FMTC605-100CM, from Fairview Microwave is in-stock and ships same day. This Fairview type N to type F cable assembly has a male to female gender configuration with 75 ohm flexible FM-SF200LL75 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMTC605-100CM type N male to type F female cable assembly operates to 3 GHz. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness. Fairview Microwave's test cables are constructed using our FM-SF200LL75 coax which is optimized for use up to 3 GHz with 75 Ohm F Type to 75 Ohm Type N connectors. This flexible coaxial cable has excellent low insertion loss along with a velocity propagation of 70%. The highly flexible cable also reduces the strain applied to your test components, making it easier to route the cables in your test setup or equipment rack. These 3 GHz test cables are available in Male and Female connectors with F Type to Type N combinations and are available in standard lengths from stock for same day shipment.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		3	GHz
VSWR			1.35:1	
Insertion Loss			1.73	
Velocity of Propagation		70		%
Dielectric Withstanding Voltage (AC)			500	Vrms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	3			GHz
Insertion Loss (Max.)	1.51	1.6	1.73			dB

Electrical Specification Notes:
 Values at 25°C, sea level.

Mechanical Specifications
Cable Assembly

Length* 39.37 in [100 cm]
 Weight 0.25 lbs [113.4 g]

Cable

Cable Type FM-SF200LL75


Configuration:

- N Male
- F Female
- FM-SF200LL75

Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- Double Shielded
- FEP Jacket
- Precision 75 Ohm F Type to 75 Ohm Type N connectors
- VSWR of 1.35:1 to 3 GHz
- 70% velocity of propagation (VoP)
- 100% VSWR tested and Hi-Pot tested to 500 volts
- Very flexible and durable
- Enhanced strain relief, heavy duty booting
- In-stock and same day shipment
- Precision F Type center conductor diameter 0.029"
- Broadband performance

Applications:

- General Purpose
- Laboratory Use
- Production testing
- RF development testing
- General lab testing
- Test rack applications

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Impedance	75 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Bare
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP
Jacket Diameter	0.195 in [4.95 mm]
One Time Minimum Bend Radius	1 in [25.4 mm]

Connectors

Description	Connector 1	Connector 2
Type	N Male	F Female
Impedance	75 Ohms	75 Ohms
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Dielectric Type	PTFE	PTFE
Outer Cond Material & Plating		Passivated Stainless Steel
Body Material & Plating	Passivated Stainless Steel	Passivated Stainless Steel
Coupling Nut Material & Plating	Passivated Stainless Steel	

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

How to Order

Part Number Configuration:

FMTC605 - xx uu

cm = Centimeters
 <blank> = Inches

Length


Example: FMTC605-12 = 12 inches long cable
 FMTC605-100cm = 100 cm long cable


75 Ohm N Male to 75 Ohm F Female Cable 75 Ohm FM-SF200LL75 Coax in 100 cm from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [75 Ohm N Male to 75 Ohm F Female Cable 75 Ohm FM-SF200LL75 Coax in 100 cm FMTC605-100CM](https://www.fairviewmicrowave.com/broadband-n-male-f-female-cable-fm-sf200ll75-coax-fmtc605-100cm-p.aspx)

URL: <https://www.fairviewmicrowave.com/broadband-n-male-f-female-cable-fm-sf200ll75-coax-fmtc605-100cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE 75 Ohm N Male to 75 Ohm F Female Cable 75 Ohm FM-SF200LL75 Coax in 100 cm		DWG NO FMTC605		CAGE CODE 3FKR5	
		CAD FILE 022916	SHEET	SCALE N/A	SIZE A 2233