

TNC Female (Jack) RF Termination (Load) with Chain, 2 Watt, DC to 12 GHz, 75 Ohm, Brass



**FMTR1193C**

**Features**

- DC to 12 GHz Frequency Range
- 75 Ohm Impedance
- TNC Female Coaxial Interface
- Max VSWR 1.25:1
- Max Power 2 Watts (CW)
- Includes Beaded Chain

**Applications**

- 8k UHD TV
- Video Distribution
- Test and Measurement

**Description**

Fairview Microwave's FMTR1193C is an RF termination (also called RF load or dummy load) that operates from DC to 12 GHz and handles up to 2 Watt (CW). Our TNC termination / load has a female gender. FMTR1193C TNC load termination offers 1.25:1 max VSWR. RF load / terminations are indispensable components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator on an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, circulators, and switches. They are also widely used in measurement systems to ensure accurate results. Fairview Microwave offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watt (CW).

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12	GHz
Impedance		75		Ohms
VSWR, Input			1.25:1	
Input Power (CW)			2	Watts
2W average power from -55°C to +70°C linearly derated to 1W at 165°C				
Dielectric Withstanding Voltage (AC)			1,500	Vrms
Operating Voltage (AC)			500	Vrms

**Mechanical Specifications**

**Size**

- Length 1.38 in [35.05 mm]
- Width 0.62 in [15.75 mm]
- Height 0.62 in [15.75 mm]
- Weight 0.2 lbs [90.72 g]

**Configuration**

- Connector TNC Female
- Mating Torque 4.1 to 6.1 in-lbs [0.46 to 0.69 Nm]
- Durability 500 Cycles

TNC Female (Jack) RF Termination (Load) with Chain, 2 Watt, DC to 12 GHz, 75 Ohm, Brass



**FMTR1193C**

**Material Specifications**

Description	Material	Plating
Connector 1 Contact	Beryllium Copper	Gold over Nickel-Phosphorus Alloy over Copper
Insulation	Teflon	
Gasket	Silicone	
Connector 1 Body	Brass	Tri-Metal over Copper
Coupling Nut	Brass	Tri-Metal over Copper
Housing	Brass	Tri-Metal over Copper
Chain	Brass	Tri-Metal over Copper

**Environmental Specifications**

**Temperature**

Operating Range

Humidity

Thermal Shock

Salt Spray

-55 to +165 deg C

Mil-STD-202, Method 106

MIL-STD-202, Method 107, Condition B

MIL-STD-202, Method 101, Condition B

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

TNC Female (Jack) RF Termination (Load) with Chain, 2 Watt, DC to 12 GHz, 75 Ohm, Brass from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [TNC Female \(Jack\) RF Termination \(Load\) with Chain, 2 Watt, DC to 12 GHz, 75 Ohm, Brass FMTR1193C](#)

URL: <https://www.fairviewmicrowave.com/rf-load-2-watts-12-ghz-chain-tnc-female-fmtr1193c-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

# FMTR1193C CAD Drawing

TNC Female (Jack) RF Termination (Load) with Chain, 2 Watt, DC to 12 GHz, 75 Ohm, Brass

