

WR-10 Waveguide Load Rated For 50 Watts, Operating from 75 GHz to 110 GHz, Constructed from Copper and Equipped with a UG-387/U-M Flange



FMW10TR002

Features

- WR-10 Waveguide
- Operating Frequency Range from 75 GHz to 110 GHz
- Low VSWR of 1.35:1 Max
- 50 Watt (CW) Average Power Handling
- UG-387/U-M Cover Flange
- Excellent Impedance Matching

Applications

- Test & Measurement
- RF & Microwave Labs
- Radar Systems
- Satellite Communications (SATCOM)
- Aerospace & Defense

Description

The FMW10TR002 is a WR-10 waveguide termination/load designed to provide a precision matched termination over the 75 to 110 GHz frequency range. It features a maximum VSWR of 1.25:1, minimizing reflections and ensuring accurate RF system performance. Constructed from painted Brass with a UG-387/U-M cover flange, this waveguide termination offers a lightweight, rugged solution suitable for laboratory, commercial, industrial, aerospace, and defense microwave applications. It is ideal for terminating unused waveguide ports, absorbing incident RF energy, and improving system impedance matching. As part of Fairview Microwave's extensive waveguide component portfolio, this termination is in stock and available for same-day shipment.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	75		110	GHz
VSWR			1.35:1	
Input Power (CW)			50	Watts
Input Power (Peak)			1	kWatts

Mechanical Specifications

Size

Length	4.09 in [103.89 mm]
Width/Dia.	1.18 in [29.97 mm]
Height	1.18 in [29.97 mm]
Weight	0.3 lbs [136.08 g]

Description	Flange	Waveguide
Designation	UG-387/U-M	WR-10
Material		Brass Copper
Plating		Gold
Finish		Grey Paint

Environmental Specifications

Temperature

Operating Range	-40 to +70 deg C
-----------------	------------------

WR-10 Waveguide Load Rated For 50 Watts, Operating from 75 GHz to 110 GHz, Constructed from Copper and Equipped with a UG-387/U-M Flange



FMW10TR0002

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

WR-10 Waveguide Load Rated For 50 Watts, Operating from 75 GHz to 110 GHz, Constructed from Copper and Equipped with a UG-387/U-M Flange from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [WR-10 Waveguide Load Rated For 50 Watts, Operating from 75 GHz to 110 GHz, Constructed from Copper and Equipped with a UG-387/U-M Flange FMW10TR0002](#)

URL: <https://www.fairviewmicrowave.com/wr-10-waveguide-termination-50-watts-75-110-ghz-fmw10tr0002>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

WR-10 Waveguide Load Rated For 50 Watts, Operating from 75 GHz to 110 GHz,
Constructed from Copper and Equipped with a UG-387/U-M Flange

