

30 dB WR-51 Waveguide Broadwall Coupler with UG Square Flange and 2.92mm Female Coupling Port from 14.5 GHz to 22 GHz in Brass

FMW51CP001-30



Features

- Three Port broadwall Waveguide Coupler
- 30±0.7 dB Nominal Coupling Level
- Integrated 2.92mm Female Connector for the coupled ports
- 14.5 GHz to 22 GHz Frequency Range
- Low VSWR < 1.25:1

Applications

- Test Benches
- Radar
- Satellite
- Microwave Radio
- Attenuation Measurements
- Power Measurements
- Source Leveling

Description

The FMW51CP001-30 is a 30 dB WR-51 three port broadwall Coupler withh integrated 2.92mm Female connectors for the coupled ports. This coupler can be mounted directly into the waveguide signal path, connected via coax to allow signal sampling /monitoring. The coupler has a typical VSWR of 1.1:1 and are made of Brass with UG Square flanges. The FMW51CP001-30 is part of a family of cross guide couplers offered by Fairview Microwave with coupling values ranging from 20 to 50 dB.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	14.5		22	GHz
Impedance		50		Ohms
Coupler				
Nominal Coupling Level		30		dB
Coupling Accuracy		±0.7		dB
Directivity	30			dB
Insertion Loss			0.2	dB
Main Line VSWR			1.1:1	
Secondary Line VSWR			1.25:1	
Input Power (CW)			350	Watts
Input Power, Peak			50	kWatts

Mechanical Specifications

Size

Length	7.48 in [189.99 mm]
Width	1.31 in [33.27 mm]
Height	1.31 in [33.27 mm]
Weight	1 lbs [453.59 g]

Interface

Waveguide Size	WR-51
Flange Type	UG Square Flange
Flange Material and Plating	Brass Copper, Passivated Stainless Steel
RF Connector Type	2.92mm Female

30 dB WR-51 Waveguide Broadwall Coupler with UG Square Flange and 2.92mm Female Coupling Port from 14.5 GHz to 22 GHz in Brass

FMW51CP001-30



Coupler Body Material and Plating
Coupler Body Plating Specification

Brass Copper, Passivated Stainless Steel
Anticorrosion grey paint

Environmental Specifications

Temperature

Operating Range
Storage Range

-40 to +70 deg C
-55 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

30 dB WR-51 Waveguide Broadwall Coupler with UG Square Flange and 2.92mm Female Coupling Port from 14.5 GHz to 22 GHz in Brass from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [30 dB WR-51 Waveguide Broadwall Coupler with UG Square Flange and 2.92mm Female Coupling Port from 14.5 GHz to 22 GHz in Brass FMW51CP001-30](#)

URL: <https://www.fairviewmicrowave.com/30db-wr51-waveguide-broadwall-coupler-ug-square-flange-22ghz-fm-w51cp001-30-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

30 dB WR-51 Waveguide Broadwall Coupler with UG Square Flange and 2.92mm Female Coupling Port from 14.5 GHz to 22 GHz in Brass

