

**Times Microwave LMR-200-FR Low Loss Flexible
Coax Cable Black FRPE Jacket**
Times Microwave Systems Coax Cable Specification
Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		5.8	GHz
Impedance		50		Ohms
Velocity of Propagation		83		%
Time Delay		1.22 [4]		ns/ft [ns/m]
Shielding Effectiveness	90			dB
DWV (DC)			1,000	Vdc
Jacket Spark			3,000	Vrms
Inner Conductor DC Resist.			5.36	Ohms/1000ft
Outer Conductor DC Resist.			4.9	Ohms/1000ft
Nominal Capacitance		24.5		pF/ft
		[80.38]		[pF/m]
Nominal Inductance		0.061		uH/ft
		[0.2]		[uH/m]
Input Power (Peak)			2.5	kWatts

Performance by Frequency Band

Description	F1	F2	F3	F4	F5	Units
Frequency	50	150	220	450	900	MHz
Attenuation, Typ	2.3 7.55	4 13.12	4.8 15.75	7 22.97	9.9 32.48	dB/100ft dB/100m
Power In (CW), Max	790	450	370	260	180	Watts

Description	F6	F7	F8	F9	F10	Units
Frequency	1.8	2.5	5.8			GHz
Attenuation, Typ	14.2 46.59	16.9 55.45	26.4 86.61			dB/100ft dB/100m
Power In (CW), Max	130	110	70			Watts

Mechanical Specifications

Diameter	0.195 in [4.95 mm]
Weight	0.026 lbs/ft [0.04 kg/m]
Min. Bend Radius (Installation)	0.5 in [12.7 mm]
Min. Bend Radius (Repeated)	2 in [50.8 mm]
Bending Moment	2 lbs-ft [2.71 N-m]
Tensile Strength	40 lbs [18.14 kg]
Flat Plate Crush	15 lbs/in [0.27 kg/mm]


Configuration:

- Low Loss, Fire Rated Flexible Cable
- 2 Shield(s)

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Construction Specifications

Description	Material and Plating	Diameter
Inner Conductor	Copper, 1 Strands	0.044 in [1.12 mm]
Conductor Type	Stranded	
Dielectric	PE	0.116 in [2.95 mm]
First Shield	Aluminum Tape	[]
Second Shield	Tinned Copper Braid	[]
Jacket	FRPE, Black	0.195 in [4.95 mm]

Environmental Specifications
Temperature

Operating Range

-40 to +185 deg C

Storage Range

-94 to +185 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:


Times Microwave LMR-200-FR Low Loss Flexible Coax Cable Black FRPE Jacket from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Times Microwave LMR-200-FR Low Loss Flexible Coax Cable Black FRPE Jacket LMR-200-FR-FT](#)


URL: <https://www.fairviewmicrowave.com/lmr200fr-low-loss-flexible-coax-cable-frpe-jacket-lmr-200-fr-ft-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/24/2022	AGANWANI



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

<div><div><div></div><div></div><div></div><div></div><div></div><div></div></div><div><div>Fairview Microwave</div><div>an INFINITE brand</div></div></div>		UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		THIRD-ANGLE PROJECTION 	
TITLE		TOLERANCES:		CABLE LENGTH (L) TOLERANCES:	
Times Microwave LMR-200-FR Low Loss Flexible Coax Cable Black FRPE Jacket		.X = ±.2 [5.08] FRACTIONS		L ≤ 12 [305] = +1 [25] / -0	
		.XX = ±.02 [.51] ± 1/32		12 [305] < L ≤ 60 [1524] = +2 [51] / -0	
		XXX = ±.005 [.13] ANGLES ± 1°		60 [1524] < L ≤ 120 [3048] = +4 [102] / -0	
				120 [3048] < L ≤ 300 [7620] = +6 [152] / -0	
				300 [7620] < L = +5%L / -0	
		ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.		SHEET 1 OF 1	
		SIZE A		SCALE N/A	
		CAGE CODE 3FKR5		DRAWN BY DZINN	
				ITEM NO. LMR-200-FR-FT	
				REV A	

T-Rev.D