

RG 400

SPECIFICATIONS

ELECTRICAL:


FREQUENCY: 12400 MHz
IMPEDANCE: 50 OHMS
CAPACITANCE (pF/m): 105
VELOCITY PROPOGATION: 70%
VOLTAGE(VMS): 1900 MAX

MIN BEND RADIUS: .984" (25mm)

OPERATING TEMPERATURE: -55° to +200°C

MATERIAL:

CENTER CONDUCTOR: Si PLATED COPPER
DIELECTRIC: PTFE
OUTER CONDUCTOR: Si PLATED COPPER DOUBLE BRAID



FREQUENCY(MHz)	ATTENUATION(>dB/1ft)
100	.04
400	.09
1000	.14
3000	.27
5000	.36
11000	.58

FAIRVIEW MICROWAVE INC.
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

RG 400

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	RG 400	--
SCALE		SHEET	

ALL DIMENSIONS IN inches(MM) Typical