

BNC Male to TNC Male MIL-DTL-17 Cable M17/183-00001 Coax in 18 Inch

FMHR0118-18



Configuration

- Connector 1: M39012/16-0013 (BNC Male)
- Connector 2: M39012/26-0010 (TNC Male)
- Cable: M17/183-00001

Features

- Max Frequency 1 GHz
- 65.9% Phase Velocity
- Polyolefin Jacket
- J-STD-Soldering
- Lot Traceability Data
- Qualified cable and connectors (QPL)
- Acceptance Test Report
- RF Test Data
- In stock and ready to ship

Applications

- General Purpose
- Laboratory Use
- Hi-Reliability
- Unmanned Systems
- Drones
- MIL-DTL-17 Requirements
- Military Electronics

Description

MIL-DTL-17 BNC (M39012/16-0013) to TNC (M39012/26-0010) cable assemblies with test reports from Fairview Microwave are part of our full line of reliable RF components available with same-day shipping. These COTS (commercial-off-the-shelf) cable assemblies using M17/183-00001 have traceable processes and materials that are recorded and provided in the included test report. The MIL-DTL-17 coaxial cable and MIL-PRF-39012 connectors are assembled with J-STD-001 soldering processes and meet WHMA-A-620 workmanship criteria. These carefully selected materials, assembly processes and test sequence ensure a dependable cable assembly for high reliability applications where the cost of failure or replacement is high. Each serialized BNC to TNC MIL-DTL-17 cable assembly is traceable to its component lots and test data ship with every cable.

This MIL-C-17 M39012/16-0013 to M39012/26-0010 cable assembly using M17/183-00001 datasheet PDF contains specifications, CAD drawing and dimensions that are shown below. Fairview Microwave offers these high reliability RF cable assemblies with test data, and many other RF, microwave and millimeter wave components which allow designers to configure and customize their signal systems however they like. Whether the need is to provide reliable MIL-DTL-17 interconnects or supporting test reports, Fairview Microwave has the right cable assemblies for the job. Fairview can also expertly build your custom cable assemblies for you and ship same day.

IPC/WHMA-A-620
MIL-DTL-17
MIL-STD-348

Requirements and Acceptance for Cable and Wire Harness Assemblies
Cables, Radio Frequency, Flexible and Semirigid, General Specification for
Radio Frequency Connector Interfaces for MIL-DTL-3643, MIL-DTL-3650, MIL-DTL-3655, MIL-DTL-25516, MIL-
PRF-31031, MIL-PRF-39012, MIL-PRF-49142, MIL-PRF...

MIL-PRF-39012
IPC J-STD-001
IPC J-STD-006

Connectors, Coaxial, Radio Frequency, General Specification for
Requirements for Soldered Electrical and Electronic Assemblies
Requirements for Electronic Grade Solder Alloys and Fluxed and Non-Fluxed Solid Solders for Electronic Soldering
Applications

SAE AS5942
SAE AS23053
SAE AS22520

Marking of Electrical Insulating Materials
Insulation Sleeving, Electrical, Heat Shrinkable, General Specifications For
Crimping Tools, Wire Termination, General Specification For

Material Specifications

| Component | Specification |
|-------------|---|
| Cable | M17/183-00001 in accordance with MIL-DTL-17 |
| Connector 1 | M39012/16-0013 in accordance with MIL-PRF-39012 |

BNC Male to TNC Male MIL-DTL-17 Cable
M17/183-00001 Coax in 18 Inch



FMHR0118-18

Material Specifications

| Component | Specification |
|---------------|---|
| Connector 2 | M39012/26-0010 in accordance with MIL-PRF-39012 |
| Heat Shrink 1 | M23053/5-106-0 in accordance with SAE AS23053 |
| Heat Shrink 2 | M23053/5-106-0 in accordance with SAE AS23053 |
| Solder | SN63 in accordance with J-STD-006 |

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|--------------------------------------|---------|---------------|---------|-----------------|
| Frequency Range | DC | | 1,000 | MHz |
| VSWR | | | 1.4:1 | |
| Velocity of Propagation | | 65.9 | | % |
| Capacitance | | 32.2 [105.64] | | pF/ft [pF/m] |
| DC Resistance Inner Conductor | | 0.97 [3.18] | | Ω/1000ft [Ω/Km] |
| Dielectric Withstanding Voltage (AC) | | | 1,500 | Vrms |

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|------|-----|-------|----|-------|
| Frequency | 50 | 100 | 400 | 1,000 | | MHz |
| Insertion Loss (Max.) | 0.18 | 0.22 | 0.4 | 0.58 | | dB |

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.06*SQRT(GHz) dB maximum for the TNC Male connector and 0.1 dB for the BNC Male connector.

Mechanical Specifications

Cable Assembly

| Description | Minimum | Typical | Maximum | Units |
|----------------------|------------|-----------------|-------------|---------|
| Length* | 18 [457.2] | 19 [482.6] | 18 [457.2] | in [mm] |
| Cable Outer Diameter | 0.191 | 0.195 | 0.199 | in |
| Weight | | 0.12906 [58.54] | 0.14 [63.5] | lbs [g] |

Cable Characteristics

| Description | Specification |
|----------------------|---------------|
| Cable Type | M17/183-00001 |
| Impedance | 50 Ohms |
| Inner Conductor Type | Stranded |

BNC Male to TNC Male MIL-DTL-17 Cable
M17/183-00001 Coax in 18 Inch

FMHR0118-18



Cable Characteristics

| Description | Specification |
|--------------------------------------|-------------------|
| Inner Conductor Material and Plating | Tinned Copper |
| Dielectric Type | PE |
| Number of Shields | 1 |
| Shield Layer 1 | Tinned Copper |
| Outer Conductor Diameter | 0.15 in [3.81 mm] |
| Jacket Material | Polyolefin |

Connector Characteristics

| Description | Connector 1 | Connector 2 |
|---------------------------------------|-------------------|-------------------|
| Type | BNC Male | TNC Male |
| Specification | MIL-PRF-39012 | MIL-PRF-39012 |
| Impedance | 50 Ohms | 50 Ohms |
| Configuration | Straight | Straight |
| Contact Material and Plating | Brass, Gold | Brass, Gold |
| Contact Plating Specification | ASTM B488 | ASTM B488 |
| Dielectric Type | Teflon | Teflon |
| Outer Conductor Material and Plating | Brass, Silver | |
| Outer Conductor Plating Specification | ASTM B700 | |
| Body Material and Plating | Brass, Silver | Brass |
| Body Plating Specification | ASTM B700 | |
| Seal Gasket Material | Silicone Rubber | Silicone Rubber |
| Contact Gage Specification | 0.210 to 0.230 in | 0.210 to 0.230 in |
| Insulator Gage Specification | 0.208 to 0.228 in | 0.208 to 0.228 in |

Mechanical Specification Notes:

Environmental Specifications

| Description | Specification |
|-----------------------------|------------------|
| Temperature Operating Range | -30 to +85 deg C |

Compliance Certifications (see [product page](#) for current document)

Process Specifications

| Process | Specification |
|-----------|---------------------------------------|
| Soldering | in accordance with J-STD-001, class 3 |
| Crimping | dies in accordance with SAE AS22520 |

BNC Male to TNC Male MIL-DTL-17 Cable
M17/183-00001 Coax in 18 Inch



FMHR0118-18

Process Specifications

| Process | Specification |
|-------------|---|
| Marking | shall meet the adherence requirements of SAE AS5942 |
| Workmanship | shall be in accordance with IPC/WHMA-A-620, class 3 |

Tests and Inspections

| Description | Sampling |
|---|--------------|
| Connector Gaging (pin and insulator position) | 100% |
| Insertion Loss | 100% |
| VSWR | 100% |
| Dielectric Withstanding Voltage (DWV) | 100% |
| Visual - workmanship, configuration and marking | 100% |
| Length | C=0, 1.5 AQL |
| Mass | C=0, 1.5 AQL |

Plotted and Other Data

Notes:
Values at 25°C, sea level.

BNC Male to TNC Male MIL-DTL-17 Cable
M17/183-00001 Coax in 18 Inch



FMHR0118-18

How to Order

Part Number Configuration:

FMHR0118 - xx uu



Example: FMHR0118-12 = 12 inches long cable
FMHR0118-100cm = 100 cm long cable

Cable Assembly Length Tolerances:

| Imperial English | | Metric | |
|---------------------|-----------------|---------------------|------------------|
| "L" ≤ 1 ft | +0.5 in / -0 in | "L" ≤ 0.3 m | +12.5 mm / -0 mm |
| 1 ft < "L" ≤ 5 ft | +1 in / -0 in | 0.3 m < "L" ≤ 1.5 m | +25 mm / -0 mm |
| 5 ft < "L" ≤ 10 ft | +2 in / -0 in | 1.5 m < "L" ≤ 3 m | +50 mm / -0 mm |
| 10 ft < "L" ≤ 25 ft | +3 in / -0 in | 3 m < "L" ≤ 7.5 m | +75 mm / -0 mm |
| 25 ft < "L" | +2%"L" / -0%"L" | 7.5 m < "L" | +2%"L" / -0%"L" |

* Cable Length = "L"

BNC Male to TNC Male MIL-DTL-17 Cable M17/183-00001 Coax in 18 Inch from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: [BNC Male to TNC Male MIL-DTL-17 Cable M17/183-00001 Coax in 18 Inch FMHR0118-18](https://www.fairviewmicrowave.com/bnc-male-tnc-male-cable-m17-183-00001-coax-fmhr0118-18-p.aspx)

URL: <https://www.fairviewmicrowave.com/bnc-male-tnc-male-cable-m17-183-00001-coax-fmhr0118-18-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMHR0118-18 CAD Drawing

BNC Male to TNC Male MIL-DTL-17 Cable M17/183-00001 Coax in 18 Inch




NOTES:

1. BLACK HEAT SHRINK WITH WHITE MARKINGS 3 PLACES.
2. CABLES ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

FM DS Rev-D4 Alt2b

| | | |
|---|--|---|
|  Fairview Microwave® an INFINITO brand | | Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.972.649.6678 |
| UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES. DIMENSIONS IN [] ARE IN MILLIMETERS. | | INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 |
| TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [0.5] ANGLES ± 1° .XXX = ±.005 [0.13] | | SCALE NONE SHEET 1 OF 1 |
| CABLE LENGTH TOLERANCES: >12 [305] ≤ 60 [1524] = +0.15 [3.8] / -0 >60 [1524] ≤ 120 [3048] = +2 [51] / -0 >120 [3048] ≤ 300 [7620] = +2.5 [63.5] / -0 | | DESCRIPTION BNC MALE TO TNC MALE MIL-DTL-17 CABLE M17/183-00001 COAX |
| ALL DIMENSIONS ARE FOR REFERENCE ONLY. UNDIMENSIONED NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY. | | SIZE A CAGE CODE 3FKR5 DRAWN BY KDANG ITEM NO. FMHR0118 |