

RA SMA Male to TNC Male MIL-DTL-17 Cable M17/183-00001 Coax in 48 Inch

FMHR0123-48



Configuration

- Connector 1: M39012/56-3129 (SMA Male Right Angle)
- Connector 2: M39012/26-0010 (TNC Male)
- Cable: M17/183-00001

Features

- Max Frequency 1 GHz
- 65.9% Phase Velocity
- Polyolefin Jacket
- J-STD-Soldering
- Lot Traceability Data
- Qualified cable and connectors (QPL)
- Acceptance Test Report
- RF Test Data
- In stock and ready to ship

Applications

- General Purpose
- Laboratory Use
- Hi-Reliability
- Unmanned Systems
- Drones
- MIL-DTL-17 Requirements
- Military Electronics

Description

MIL-DTL-17 SMA (M39012/56-3129) to TNC (M39012/26-0010) cable assemblies with test reports from Fairview Microwave are part of our full line of reliable RF components available with same-day shipping. These COTS (commercial-off-the-shelf) cable assemblies using M17/183-00001 have traceable processes and materials that are recorded and provided in the included test report. The MIL-DTL-17 coaxial cable and MIL-PRF-39012 connectors are assembled with J-STD-001 soldering processes and meet WHMA-A-620 workmanship criteria. These carefully selected materials, assembly processes and test sequence ensure a dependable cable assembly for high reliability applications where the cost of failure or replacement is high. Each serialized SMA to TNC MIL-DTL-17 cable assembly is traceable to its component lots and test data ship with every cable.

This MIL-C-17 M39012/56-3129 to M39012/26-0010 cable assembly using M17/183-00001 datasheet PDF contains specifications, CAD drawing and dimensions that are shown below. Fairview Microwave offers these high reliability RF cable assemblies with test data, and many other RF, microwave and millimeter wave components which allow designers to configure and customize their signal systems however they like. Whether the need is to provide reliable MIL-DTL-17 interconnects or supporting test reports, Fairview Microwave has the right cable assemblies for the job. Fairview can also expertly build your custom cable assemblies for you and ship same day.

Referenced Specifications

IPC/WHMA-A-620	Requirements and Acceptance for Cable and Wire Harness Assemblies
MIL-DTL-17	Cables, Radio Frequency, Flexible and Semirigid, General Specification for
MIL-STD-348	Radio Frequency Connector Interfaces for MIL-DTL-3643, MIL-DTL-3650, MIL-DTL-3655, MIL-DTL-25516, MIL-PRF-31031, MIL-PRF-39012, MIL-PRF-49142, MIL-PRF...
MIL-PRF-39012	Connectors, Coaxial, Radio Frequency, General Specification for
IPC J-STD-001	Requirements for Soldered Electrical and Electronic Assemblies
IPC J-STD-006	Requirements for Electronic Grade Solder Alloys and Fluxed and Non-Fluxed Solid Solders for Electronic Soldering Applications
SAE AS5942	Marking of Electrical Insulating Materials
SAE AS23053	Insulation Sleeving, Electrical, Heat Shrinkable, General Specifications For
SAE AS22520	Crimping Tools, Wire Termination, General Specification For

RA SMA Male to TNC Male MIL-DTL-17 Cable
M17/183-00001 Coax in 48 Inch



FMHR0123-48

Material Specifications

Component	Specification
Cable	M17/183-00001 in accordance with MIL-DTL-17
Connector 1	M39012/56-3129 in accordance with MIL-PRF-39012
Connector 2	M39012/26-0010 in accordance with MIL-PRF-39012
Heat Shrink 1	M23053/5-106-0 in accordance with SAE AS23053
Heat Shrink 2	M23053/5-106-0 in accordance with SAE AS23053
Solder	SN63 in accordance with J-STD-006

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation		65.9		%
Capacitance		32.2 [105.64]		pF/ft [pF/m]
DC Resistance Inner Conductor		0.97 [3.18]		Ω/1000ft [Ω/Km]
Dielectric Withstanding Voltage (AC)			1,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	400	1,000		MHz
Insertion Loss (Max.)	0.21	0.33	0.82	1.33		dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable used in this assembly. The Insertion Loss includes an estimated insertion loss of $0.06 \cdot \text{SQRT}(\text{GHz})$ dB maximum for the TNC Male connector and $0.15 \cdot \text{SQRT}(\text{GHz})$ dB for the SMA Male right angle connector.

Mechanical Specifications

Cable Assembly

Description	Minimum	Typical	Maximum	Units
Length*	48 [121.92]	49 [124.46]	48 [121.92]	in [cm]
Cable Outer Diameter	0.191	0.195	0.199	in
Weight		[0]	0.21 [95.25]	lbs [g]

Cable Characteristics

Description	Specification
Cable Type	M17/183-00001

RA SMA Male to TNC Male MIL-DTL-17 Cable
M17/183-00001 Coax in 48 Inch



FMHR0123-48

Cable Characteristics

Description	Specification
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Tinned Copper
Dielectric Type	PE
Number of Shields	1
Shield Layer 1	Tinned Copper
Outer Conductor Diameter	0.15 in [3.81 mm]
Jacket Material	Polyolefin

Connector Characteristics

Description	Connector 1	Connector 2
Type	SMA Male Right Angle	TNC Male
Specification	MIL-PRF-39012	MIL-PRF-39012
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	ASTM B488	ASTM B488
Dielectric Type	Teflon	Teflon
Body Material and Plating	Steel, Gold	Brass
Body Plating Specification	ASTM B488	
Coupling Nut Material and Plating	Steel, Passivated	
Coupling Nut Plating Specification	AMS-QQ-P-35	
Seal Gasket Material	Silicone Rubber	Silicone Rubber
Contact Gage Specification	0 in min	0.210 to 0.230 in
Insulator Gage Specification	0 in min	0.208 to 0.228 in

Mechanical Specification Notes:

Environmental Specifications

Description	Specification
Temperature Operating Range	-30 to +85 deg C

RA SMA Male to TNC Male MIL-DTL-17 Cable
M17/183-00001 Coax in 48 Inch



FMHR0123-48

Compliance Certifications (see [product page](#) for current document)

Process Specifications

Process	Specification
Soldering	in accordance with J-STD-001, class 3
Crimping	dies in accordance with SAE AS22520
Marking	shall meet the adherence requirements of SAE AS5942
Workmanship	shall be in accordance with IPC/WHMA-A-620, class 3

Tests and Inspections

Description	Sampling
Connector Gaging (pin and insulator position)	100%
Insertion Loss	100%
VSWR	100%
Dielectric Withstanding Voltage (DWV)	100%
Visual - workmanship, configuration and marking	100%
Length	C=0, 1.5 AQL
Mass	C=0, 1.5 AQL

Plotted and Other Data

Notes:
Values at 25°C, sea level.

RA SMA Male to TNC Male MIL-DTL-17 Cable
M17/183-00001 Coax in 48 Inch



FMHR0123-48

How to Order

Part Number Configuration:

FMHR0123 - xx uu



Example: FMHR0123-12 = 12 inches long cable
FMHR0123-100cm = 100 cm long cable

Cable Assembly Length Tolerances:

Imperial English		Metric	
"L" ≤ 1 ft	+0.5 in / -0 in	"L" ≤ 0.3 m	+12.5 mm / -0 mm
1 ft < "L" ≤ 5 ft	+1 in / -0 in	0.3 m < "L" ≤ 1.5 m	+25 mm / -0 mm
5 ft < "L" ≤ 10 ft	+2 in / -0 in	1.5 m < "L" ≤ 3 m	+50 mm / -0 mm
10 ft < "L" ≤ 25 ft	+3 in / -0 in	3 m < "L" ≤ 7.5 m	+75 mm / -0 mm
25 ft < "L"	+2%"L" / -0%"L"	7.5 m < "L"	+2%"L" / -0%"L"

* Cable Length = "L"

RA SMA Male to TNC Male MIL-DTL-17 Cable M17/183-00001 Coax in 48 Inch from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: [RA SMA Male to TNC Male MIL-DTL-17 Cable M17/183-00001 Coax in 48 Inch FMHR0123-48](#)

URL: <https://www.fairviewmicrowave.com/ra-sma-male-tnc-male-cable-m17-183-00001-coax-fmhr0123-48-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMHR0123-48 CAD Drawing

RA SMA Male to TNC Male MIL-DTL-17 Cable M17/183-00001 Coax in 48 Inch



REVISION		DATE	CHANGED BY	APPROVED
ZONE	REV	7/10/2024	KDANG	AGANWANI
	B			
DESCRIPTION				
ECO-13683				

 an INFINITO® brand		Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.972.649.6678	
INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5			
SCALE		NONE	
SHEET		1 OF 1	
DESCRIPTION RA SMA MALE TO TNC MALE MIL-DTL-17 CABLE M17/183-00001 COAX			
SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	3FKR5	KDANG	FMHR0123
REV	REV		REV
B	B		B

UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES AND TRAILING DIMENSIONS ARE IN MILLIMETERS.

TOLERANCES:
 .X = ±.2 (5) FRACTIONS ± 1/32
 .XX = ±.02 (0.5) ANGLES ± 1°
 .XXX = ±.005 (0.13)

CABLE LENGTH TOLERANCES:
 ≤ 12 (305) ±.60 (15.24) = +0.15 (3.8) / -0
 > 12 (305) ≤ 60 (1524) = +1.25 (31.75) / -0
 > 60 (1524) ≤ 120 (3048) = +2.5 (63.5) / -0
 > 120 (3048) ≤ 300 (7620) = +5.0 (127) / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY. UNDIMENSIONED/NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.

NOTES:
 1. BLACK HEAT SHRINK WITH WHITE MARKINGS 3 PLACES.
 2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVISION CONTRARY TO U.S. LAW PROHIBITED.

FM 06 Rev-D4 Alt2b