

SPECIFICATIONS


ELECTRICAL

FREQUENCY: 0-12.4 GHZ
IMPEDANCE: 50 OHMS
VSWR: 1.25:1 MAX

MECHANICAL

MATERIALS BODY NICKLE PLATED BRASS
MATERIALS CONTACTS Au PLATING
DIELECTRIC: TEFLON
DURABILITY: 500 CYCLES MIN
INTERFACE: MIL-STD-348A

TYPE N JACK



TNC JACK

S. M. ELECTRONICS

FAIRVIEW, TX WWW.SMELECTRONICS.US

TITLE

N/F-TNC/F ADAPTER

SIZE A	CAGE CODE 3FKR5	DWG NO SM4145	REV --
------------------	--------------------	-------------------------	-----------

SCALE	SHEET
-------	-------