

N - 7/16 ADAPTER

SM4682

SPECIFICATIONS


ELECTRICAL

FREQUENCY: 0-6 GHZ
IMPEDANCE: 50 OHMS
VSWR: 1.15:1 MAX


MECHANICAL

MATERIALS BODY: TRIMETAL PLATED BRASS
MATERIALS CONTACTS SI PLATING
RECOMMENDED TORQUE 7-16 221 IN-LBS
DURABILITY: 500 CYCLES MIN
INTERFACE: MILS-STD-348
OPERATING TEMP: -55° TO +120° C

ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

N (F) - 7/16 (M) ADAPTER

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SM4682	..
SCALE			SHEET