

SMA-SMA ADAPTERS 27GHZ

SM4964

SPECIFICATIONS

ELECTRICAL

50 OHMS

VSWR 1.20:1 MAX @ 27 GHZ

FREQUENCY: 0-27 GHZ

MECHANICAL

500 CYCLES MIN

RECOMMENDED TORQUE: 7-9 IN-LBS

INTERFACE: MIL-STD-348A

ENVIRONMENTAL

-65 DEG C TO +100 DEG C

CORROSION: MIL-STD 202

VIBRATION: MIL-STD 202

MATERIALS



BODY PASSIVATED STAINLESS STEEL

CONTACTS: BeCu

CONTACT PLATING: Au MIL-G-45204

ROHS COMPLIANT

MEASUREMENTS BELOW ARE TYPICAL



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA ADAPTERS 27GHZ

SIZE

A

CAGE CODE

3FKR5

DWG NO

SM4964

REV

--

SCALE

SHEET

ALL DIMENSIONS IN inches(MM) Typical