

0 to 30 dB WR-19 Waveguide Continuously Variable Attenuator From 40 GHz To 60 GHz Dial And UG383/U-Mod Flange

Electrical Specifications*

Description	Min	Typ	Max	Units
Frequency Range	40		60	GHz
Impedance		50		Ohms
Typical Attenuation Value	0		30	dB
Insertion Loss			0.6	dB

Values at 25°C, sea level

Mechanical Specifications

Flange 1

Interface	UG383/U-Mod
Material	Copper
Plating	Gold
Color	Gold

Waveguide

Interface	WR-19
Material	Copper
Plating	Gold
Color	Gold

Flange 2

Interface	UG383/U-Mod
Material	Copper
Plating	Gold
Color	Gold

Size

Length	2.5 in [[63.5 mm]]
Width	1.125 in [[28.58 mm]]
Height	2.5625 in [[65.09 mm]]

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant	Yes
----------------	-----

Plotted and Other Data

Notes:

- Values at 25 °C, sea level




Features:

- Design: Continuously Variable Attenuator
- Waveguide: WR-19
- Flange: UG383/U-Mod
- Body Material and Plating: Copper, Gold

Fairview Microwave
1130 Junction Dr. #100
Allen, TX 75013
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data




0 to 30 dB WR-19 Waveguide Continuously Variable Attenuator From 40 GHz To 60 GHz Dial And UG383/U-Mod Flange from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [0 to 30 dB WR-19 Waveguide Continuously Variable Attenuator From 40 GHz To 60 GHz Dial And UG383/U-Mod Flange SMW19AT001-30](http://www.fairviewmicrowave.com/0-to-30-dB-WR-19-Waveguide-Continuously-Variable-Attenuator-From-40-GHz-To-60-GHz-Dial-And-UG383-U-Mod-Flange-SMW19AT001-30)

URL: <http://www.fairviewmicrowave.com/30-db-wr-19-waveguide-step-attenuator-60-ghz-smw19at001-30-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN: [mm]
TOLERANCES ARE: inches
.XX ± .02 [±.51]
.XX ± .005 [±.13]

* THESE DIMENSIONS AND TOLERANCES
SUPERSEDE NOTE #1 ON TITLE BLOCK.

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE 0 to 30 dB WR-19 Waveguide Continuously Variable Attenuator From 40 GHz To 60 GHz Dial And UG383/ U-Mod Flange	DWG NO SMW19AT001-30		CAGE CODE 3FKR5		
	CAD FILE 032315	SHEET	SCALE N/A	SIZE A	200