

FM-SR086CUTN-CL-BULK DATA SHEET

RG405 Type .086 Semi-Rigid Coax Cable with a Tin Plated Copper Outer Conductor in Coiled Sections

.086 diamater semi-rigid coaxial cable is the cable of choice for many RF and Microwave engineers. 0.086 cables sometimes referred to as RG405 based on the mil specification for semi-rigid cable of this diameter has a maximum operating frequency of 40 GHz. This form factor is widely used in the RF industry and many connector series and configurations are available for this cable. Because of the solid copper wall design the cable can be formed using proper tooling with a minimum inside bend radius of .05 inches.

Electrical Specifications

Description	Min	Min Typ Max		Units	;	
-	DC		/ 1-	40	GHz	T
Frequency Range	DC			40		
Impedance			50		Ohms	
DWV (AC)			5,000		Vrms	

Performance by Frequency Band

Description	F1	F2	F3	F4	F5	Units
Frequency	1	10	20			GHz
Attenuation, Typ	22 72.18	80 262.47	120 393.7			dB/100ft dB/100m
Power In (CW), Max	130	35	20			Watts

Mechanical Specifications

Min. Bend Radius (Installation)

Construction Specifications Description **Material and Plating** Diameter Inner Conductor Copper Clad Steel, Silver 0.02 in [0.51 mm] Conductor Type Solid Dielectric PTFE 0.066 in [1.68 mm] Outer Conductor Copper, Tin 0 in [0 mm] Jacket White []

Environmental Specifications

Temperature Operating Range

-55 to +125 deg C

0.05 in [1.27 mm]

Compliance Certifications (see product page for current document)

Plotted and Other Data Notes: Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com

REV 1.0 Page 1 of 3 Copyright © 2020



Configuration:

- Semi-Rigid Cable
- 0 Shield(s)

Features:

- Silver Plated Copper Clad Steel center conductor
- PTFE dielectric material
- Copper Tinned Outer Conductor
- Operating to 40 GHz
- Minimum inside bend radius of .05 inches
- ROHS compliant

Applications:

- RF and Microwave Cable Assemblies to 40 GHz
- Preformed cable assemblies to insure fit and layout
- Test Equipment port jumpers

Fairview Microwave



FM-SR086CUTN-CL-BULK DATA SHEET

RG405 Type .086 Semi-Rigid Coax Cable with a Tin Plated Copper Outer Conductor in Coiled Sections from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: RG405 Type .086 Semi-Rigid Coax Cable with a Tin Plated Copper Outer Conductor in Coiled Sections FM-SR086CUTN-CL-BULK

URL: https://www.fairviewmicrowave.com/rg405-type-.086-semi-rigid-coax-cable-tin-plated-copper-fm-sr086cutn-clbulk-p.aspx




301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Fairview Microwave



FM-SR086CUTN-CL-BULK DATA SHEET



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689