an INFINIT[©] brand

FM-SR086TBJ-BULK DATA SHEET

Formable .086 Formable Coax Cable Black FEP Jacket

Formable semi-rigid coax is a hand formable version of standard semi-rigid that does not require complicated and costly preformed cable assemblies. Because the dimensions and electrical characteristics are so closely matched to semi-rigid coax, standard semi-rigid connectors can be used. The tin soaked copper braid outer shield provides excellent RF shielding. FEP Jacket reduces the chance of shorting exposed contacts or circuit conductors.

Electrical Specifications

Description	Min	Т	ур	Max	Units	
Frequency Range	DC			61	GHz	
Impedance		5	50		Ohms	
Velocity of Propagation		69	9.5		%	
Time Delay		1.43	[4.69]	ns/ft [ns/m]	
Shielding Effectiveness	100				dB	
Operating Voltage (AC)				1,500	Vrms	
Inner Conductor DC Resi	st.			65.7	Ohms/1000ft	
Outer Conductor DC Res	ist.			10.2	Ohms/1000ft	
Nominal Capacitance		Ĩ	29		pF/ft	
		[95.14]			[pF/m]	

Performance by Frequency Band

-	-	-				
Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	5	10	20	GHz
Attenuation, Typ	15 49.21	22.5 73.82	54.9 180.12	81.2 266.4	120 393.7	dB/100ft dB/100m
Power In (CW), Max	173. <mark>5</mark>	121.5	52.2	35.8	24.3	Watts

Mechanical Specifications

Diameter	
Weight	

0.105 in [2.67 mm] 0.014 lbs/ft [0.02 kg/m]

Min. Bend Radius (Installation) Min. Bend Radius (Repeated) 0.5 in [12.7 mm] 0.787 in [19.99 mm]

Construction Specifications

Description	Material and Plating	Diameter	
Inner Conductor	Copper Clad Steel, Silver, 1 Strands	0.02 in [0.51 mm]	
Conductor Type	Solid		
Dielectric	PTFE	0.062 in [1.57 mm]	
Outer Conductor	Tinned Copper Composite Braid	0 in [0 mm]	
Jacket	FEP, Black	0.105 in [2.67 mm]	



Configuration:

- Formable Cable
- 1 Shield(s)

Features:

- Dimensionally the same as standard solid outer conductor semirigid coax
- Standard semi-rigid connectors can be used
- Cable is hand formable and does not require special tools to bend
- Connectors are easily soldered to Tin soaked outer conductor
- Cable can be formed more than once without damage to outer conductor
- High RF Shielding >100 dB

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Temperature Operating Range

-55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data Notes:

Formable .086 Formable Coax Cable Black FEP Jacket from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Formable .086 Formable Coax Cable Black FEP Jacket FM-SR086TBJ-BULK

URL: https://www.fairviewmicrowave.com/invalid-alias-formable-coax-cable-fep-jacket-fm-sr086tbj-bulk-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Fairview Microwave







301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689