

75 Ohm F Female Load Calibration Kit Component for General Purpose Up to 3 GHz

The new FMTR1004 from Fairview Microwave is designed to withstand daily use in high-traffic environments such as in the testing lab or on the production floor. This cost effective calibration kit component provides reliable and accurate instrument tuning for all of your test and measurement requirements. Fairview Microwave carries a broad selection of off-the-shelf calibration kits and T&M components all of which ship the same day you order them.

Configuration

Connector	F Female
Component Type	Load
Impedance	75 Ohms
Frequency Range	DC to 3 GHz

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC - 3000			MHz
Impedance	75			Ohm
Return Loss, DC - 1000 MHz	38	40		dB
Return Loss, 1001 - 3000 MHz	36	38		dB

Mechanical Specifications

Item	Description	Units
Housing	Copper Tube	
Connector	75 Ohm F Type Female	
Connector Screw Thread	W3/8"-32 UNEF	Inch
Dimensions	0.697 [17.7] ϕ , 1.532 [38.9] L	Inch [mm]
Net Weight	45.8	g



Features:

- Functional from DC to 3 GHz
- See FMCK1002 for full standard kit which includes (7) F Type short-open-load-thru (SOLT) components
- Suitable for many 75 Ohm network analyzers including, but not limited to:
- Agilent / HP (8711/8713/8714, 8753E-075, E5061A, E5062A, E 5061B)
- Rohde & Schwarz (R&S ZVL3-75 [9KHz - 3GHz, Built-in 85039B Calibration Kit Option])
- Tianda (TD3618C/E)
- OuFu (OF7631B, OF7633B)
- Copper Mountain (7530)
- Deviser (NA7300B, NA7100B)
- EI41 (AV36580A)
- PNA (PNA3766)

Applications:

- VNA, Full 2-Port CAL
- VNA, Thru CAL
- VNA, Substitution CAL Method
- Test & Measurement
- Lab Equipment Accessories
- Engineering Test and Evaluation
- General Purpose Test and Evaluation


Fairview Microwave
1130 Junction Dr. #100
Allen, TX 75013
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

General Instructions and Usage Notes

#	Notes
1	Keep provided protective red caps installed when not in use.
2	Store in climate controlled environment.
3	Always keep connectors clean.
4	Avoid touching the connector interface.
5	Use caution when handling.
6	For female components, do not insert male pin greater than 0.037" [.94 mm]. Failure to comply will result in damage to the female connector.
7	When mating, always ensure that the components to be interconnected remain in a fixed position while rotating only the coupling nut slowly to mate the connectors.
8	When de-mating, always ensure that the interconnected components remain in a fixed position while rotating only the coupling nut slowly to de-mate the connectors.
9	Visually inspect the connector threads prior to use. If needed, clean the center conductor pin and outer conductor with alcohol to remove any debris that may be present. Be sure to apply the alcohol in a circular motion with a lint-free cloth or applicator.
10	Use at room temperature.

Typical Performance Data

FMTR1004 Return Loss
Span: 3 GHz



Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant Yes
REACH Compliant 06/16/2014

Plotted and Other Data


Notes:
• Values at 25 °C, sea level

75 Ohm F Female Load Calibration Kit Component for General Purpose Up to 3 GHz from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [75 Ohm F Female Load Calibration Kit Component for General Purpose Up to 3 GHz FMTR1004](http://www.fairviewmicrowave.com/75ohm-f-female-calibration-kit-component-load-3-ghz-fmtr1004-p.aspx)

URL: <http://www.fairviewmicrowave.com/75ohm-f-female-calibration-kit-component-load-3-ghz-fmtr1004-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE 75 Ohm F Female Load Calibration Kit Component for General Purpose Up to 3 GHz	DWG NO		CAGE CODE		
	FMTR1004		3FKR5		
	CAD FILE	012815	SHEET	SCALE	N/A
				SIZE	A
					2233