

F-Type Male (Plug) RF Termination (Load), 2 Watt, DC to 12 GHz, 75 Ohm, Brass



FMTR1194

Features

- DC to 12 GHz Frequency Range
- 75 Ohm Impedance
- F-Type Male Coaxial Interface
- Max VSWR 1.25:1
- Max Power 2 Watts (CW)

Applications

- 8k UHD TV
- Video Distribution
- Test and Measurement

Description

Fairview Microwave's FMTR1194 is an RF termination (also called RF load or dummy load) that operates from DC to 12 GHz and handles up to 2 Watt (CW). Our F-Type termination / load has a male gender. FMTR1194 F-Type load termination offers 1.25:1 max VSWR. RF load / terminations are indispensable components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator on an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, circulators, and switches. They are also widely used in measurement systems to ensure accurate results. Fairview Microwave offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watt (CW).

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12	GHz
Impedance		75		Ohms
VSWR, Input			1.25:1	
Input Power (CW)			2	Watts
Dielectric Withstanding Voltage (AC)			1,500	Vrms
Operating Voltage (AC)			500	Vrms

Mechanical Specifications

Size

Length	1.39 in [35.31 mm]
Width	0.62 in [15.75 mm]
Height	0.62 in [15.75 mm]
Weight	0.15 lbs [68.04 g]

Configuration

Connector	F Male
Mating Torque	15 to 20 in-lbs [1.70 to 2.26 Nm]
Durability	500 Cycles

Material Specifications

Description	Material	Plating
Connector 1 Contact	Beryllium Copper	Gold over Nickel-Phosphorus Alloy over Copper

F-Type Male (Plug) RF Termination (Load), 2 Watt, DC to 12 GHz, 75 Ohm, Brass



FMTR1194

Material Specifications

Description	Material	Plating
Insulation	PS	
Connector 1 Body	Brass	Tri-Metal over Copper
Housing	Brass	Tri-Metal over Copper

Environmental Specifications

Temperature

Operating Range

-55 to +100 deg C

Humidity

Mil-STD-202, Method 106

Thermal Shock

MIL-STD-202, Method 107, Condition B

Salt Spray

MIL-STD-202, Method 101, Condition B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

F-Type Male (Plug) RF Termination (Load), 2 Watt, DC to 12 GHz, 75 Ohm, Brass from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [F-Type Male \(Plug\) RF Termination \(Load\), 2 Watt, DC to 12 GHz, 75 Ohm, Brass FMTR1194](#)

URL: <https://www.fairviewmicrowave.com/rf-load-2-watts-12-ghz-f-male-fmtr1194-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMTR1194 CAD Drawing
F-Type Male (Plug) RF Termination (Load), 2 Watt, DC to 12 GHz, 75 Ohm, Brass

