

6-11 dBi Omni Antenna 2.4-2.5 GHz, 5.1-5.8 GHz, N Type Female PVC Radome, 1.6:1 Max VSWR, 4 Port

The Fairview Microwave FM510M1008 is a professional high gain dual band/dual polarity omnidirectional base station antenna designed and optimized for 2.4 and 5 GHz frequencies. This antenna is ideally suited for multipoint applications where long range and wide coverage is desired. The DPU series stands out from the competition since they are true 360 degree omni directional antennas which feature patent pending technology.

The FM510M1008 is actually four antennas in one, a 2.4 GHz dual polarized antenna and a 5 GHz dual polarized antenna together in a single radome. Each frequency features separate feeds for both horizontal and vertical polarities, four N-Female connectors total. This antenna incorporates advanced dual polarization technology that allows for the interoperability of two radio transmit and receive paths. This technology allows for the attenuation of unwanted signals from adjacent channels and/or co-located equipment.

The FM510M1008 construction features a heavy-duty UV resistant PVC radome for durability and aesthetics. Designed to operate in the harshest of environments, the FM510M1008 far exceeds other omnidirectional antennas. The included mounting system features twin heavy-duty mounting clamps and bolts for superior strength.

Configuration

Design	Omni
Gain	6 to 6 dBi
Polarization	Vertical/Horizontal
Connector Type	N Female
Interface 2	N Female
Interface 3	N Female
Interface 4	N Female
Number of Ports	4
Lightning Protection	DC Ground/DC Oen

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	2,400		5,800	MHz
Input VSWR			1.6:1	
Impedance		50		Ohms
Gain		6		dBi
Isolation	28			dB
Input Power			100	Watts

Specifications by Frequency

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	2.4-2.5	5.1-5.8				GHz
Gain	6	11				dBi
Horiz. Beam Width	360	360				Degrees
Vert. Beam Width	25	6.5				Degrees
VSWR	1.6:1	1.8:1				
Max Input Power	100	100				Watts



Features:

- True 360 degree omni directional antennas which feature patent pending technology
- Dual polarity/dual frequency feed system in single enclosure
- MIMO - Multiple-Input and Multiple-Output, separate inputs for 2.4 GHz and 5 GHz - four connectors total
- UV-Resistant radome for all-weather operation
- Heavy duty industrial grade design

Applications:

- 2.4/5 GHz IEEE 802.11a/b/g and 802.11ac applications
- Supports 1x2, 2x2 and 4x4 MIMO AP/Routers
- WiMax, WISP and WiFi applications
- Wireless video systems
- Point-to-multipoint applications

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Mechanical Specifications

Radome Material	PVC
Size	
Radome Diameter	2.9 in [73.66 mm]
Length	49.2 in [124.97 cm]
Width	2.9 in [73.66 mm]
Height	2.9 in [73.66 mm]
Mounting Mast Diameter	1.6 to 3.5 in [40.64 to 88.90 mm]
Weight	32.8 lbs [14.88 kg]

Mechanical Specification Notes:
Radome material is UV-resistant PVC.

Environmental Specifications

Temperature	
Operating Range	-40 to +60 deg C
Wind Loading	130 MPH [209.21 KPH]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

6-11 dBi Omni Antenna 2.4-2.5 GHz, 5.1-5.8 GHz, N Type Female PVC Radome, 1.6:1 Max VSWR, 4 Port from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [6-11 dBi Omni Antenna 2.4-2.5 GHz, 5.1-5.8 GHz, N Type Female PVC Radome, 1.6:1 Max VSWR, 4 Port FM510M1008](#)

URL: <https://www.fairviewmicrowave.com/6-dbi-omni-antenna-2.4-2.5-ghz-5.1-5.8-ghz-n-tyfm-female-1.6-1-max-vswr-4-port-fm510m1008-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

