


Adjustable Phase Shifter, DC to 4GHz, With an Adjustable Phase of 180 Deg. Per GHz with N-type connector

Fairview Microwave FM82P5017 is a phase shifter that has phase adjustment range of 180 degrees per GHz with precision rotary dial design for controllable phase adjustment across a frequency range from 0 to 4GHz. With N-Type female connectors, this RF phase shifter design is tried and true technology that offers exceptional RF performance characteristics that include 2 dB maximum insertion loss and a maximum VSWR of 1.5:1. Phase shifters are part of Pasternack's comprehensive RF passive product offerings which are available in stock and ready for same-day shipment.



Electrical Specifications (Values at +25° C, Sea Level)

Frequency RangeDC4GHzImpedance50OhmPhase Shift0720DegreePhase Adjustment0180Deg/GInput VSWR1.5:1Output VSWRInsertion Loss2Input Power, CW100Wat					
Impedance50OhmPhase Shift0720Phase Adjustment0180Deg/G1.5:1Output VSWR1.5:1Insertion Loss2Input Power, CW100	Description	Min	Тур	Max	Units
Phase Shift0720DegreePhase Adjustment0180Deg/GInput VSWR1.5:10Output VSWR11Insertion Loss2dBInput Power, CW100Wat	Frequency Range	DC		4	GHz
Phase Adjustment0180Deg/GInput VSWR1.5:10Output VSWR11Insertion Loss2dBInput Power, CW100Wat	Impedance		50		Ohms
Input VSWR 1.5:1 Output VSWR 1 Insertion Loss 2 Input Power, CW 100	Phase Shift	0		720	Degrees
Output VSWR Insertion Loss 2 dB Input Power, CW 100 Wat	Phase Adjustment	0		180	Deg/GHz
Insertion Loss 2 dB Input Power, CW 100 Wat	Input VSWR			1.5:1	
Input Power, CW 100 Wat	Output VSWR				
	Insertion Loss			2	dB
Input Power, Peak 5 kWat	Input Power, CW			100	Watts
	Input Power, Peak			5	kWatts

5µs pulse, 1% duty cycle

Mechanical Specifications

Size Length Width/Diameter Height Weight Body Material and Plating **Configuration** Input Connector Output Connector

14.65 in [372.11 mm] 2.99 in [75.95 mm] 1.2 in [30.48 mm] 3.8 lbs [1.72 kg] Aluminum

N Female N Female

Environmental Specifications

remperature	
Operating Range	-10 to 50 deg C
Storage Range	-40 to 70 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

DATA SHEET

FM82P5017



Features:

- Phase Tuning Range:
 0 to 720 degrees
- Rotary Dial Design for Continuous Adjustment
- Frequency Range from DC to 4GHz
- N-Type Female Connectorized Design
- Max VSWR 1.5:1
- Max Power Rating: 100 Watts (CW)
- Insertion Loss: 2 dB Max

Applications:

- Test & Measurements
- Radar Development
- Military Communications Systems
- Phase Array Antenna System
- Satellite Communications

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






Adjustable Phase Shifter, DC to 4GHz, With an Adjustable Phase of 180 Deg. Per GHz with N-type connector from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Adjustable Phase Shifter, DC to 4GHz, With an Adjustable Phase of 180 Deg. Per GHz with N-type connector FM82P5017


URL: https://www.fairviewmicrowave.com/n-adjustable-phase-shifter-dc-4-ghz-fm82p5017-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689