

FMAM63019 DATA SHEET

1.2 dB NF Input Protected Low Noise Amplifier, Operating from 2 GHz to 6 GHz with 40 dB Gain, 14 dBm P1dB and SMA

The FMAM63019 is an Input Protected broadband Low Noise amplifier operating across 2 GHz to 6 GHz and is rated up to 1 Watt RF input power handling. The 50 ohm design uses a PIN Diode limiter circuit on the input stage and 3 pHEMT transistor gain stages, along with series DC blocking capacitors on the input/output RF ports. Impressive typical performacne includes 40 dB small signal gain with excellent gain flatness, 1.2 dB noise figure, and an output P1dB of +14 dBm. The amplifier requires a single +12 Vdc supply, and has internal voltage regulation and low DC power consumption. The rugged Mil Grade aluminum package supports SMA female connectors, DC feedthru pin, and has an operational temperature range of -40°C to +75°C.

Electrical Specifications (TA = +25°C , DC Voltage = +12Vdc , DC Current = 90mA)

Description		Min	Тур	Max	Unit
Frequency Range		2		6	GHz
Small Signal Gain		37	40	43	dB
Gain Flatness			±1	±1.25	dB
Gain Variance at OTR*			1.5		dB
Output at 1 dB Compress	ion Point	+12	+14		dBm
Noise Figure			1.2	1.6	dB
Input VSWR			1.5:1	2:1	
Output VSWR			1.6:1	2:1	
Reverse Isolation		55	60		dB
Spurious				-70	dBc
Input Power (CW)				+30	dBm
Operating DC Voltage		+8	+12	+15	Volts
Operating DC Current		80	90	110	mA
Operating Temperature Ra	ange	-40		+75	°C
		· ·			

^{*}OTR= Base Plate Operating Temperature Range

Absolute Maximum Rating

Parameter	Rating		
DC Voltage	+15V		
RF Input Power	+30dBm		
Storage Temperature	-55~+125°C		

Operating Temperature

-40~+75°C

ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in approved ESD Workstation.

Mechanical Specifications

Size
Length 1.7 in [43.18 mm]
Width 0.95 in [24.13 mm]
Height 0.375 in [9.53 mm]
Input Connector SMA Female
Output Connector SMA Female



Features:

- Input Protected Low Noise Amplifier
- Frequency Range 2 GHz to 6 GHz
- 1 Watt Input Power Handling
- PIN Diode Limiter and pHEMT Semiconductor Technology
- DC Blocking Capacitors on the Input/Output RF Ports
- Small Signal Gain 40 dB
- 1.2 dB Noise Figure
- Output P1dB +14.0 dBm
- Nominal DC Voltage +12Vdc
- DC Current 90 mA
- 50 Ohm design
- -40°C to +75°C Operating Temperature
- SMA Female Connectors
- Rugged Mil Grade Aluminum Package Design

Applications:

- Military & Commercial Communication Systems
- Microwave Radio Systems
- Radar Systems
- · Test & Measurement
- · Research & Development
- RF Wideband Front Ends

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





Environmental Specifications Temperature

Operating Range -40 to +75 deg CStorage Range -55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

· Values at 25 °C, sea level

Amplifier Power-up Precautions


- 1.) Confirm that proper ESD precautions and controls are always in place before handling any Amplifier module.
- 2.) Confirm adequate thermal management is in place to effectively dissipate heat away from the Amplifier package. The Amplifier operational baseplate temperature must be within the operational temperature range stated in the Amplifier datasheet. Depending on the design and thermal requirements, using a heatsink with cooling fan is always recommended for safe reliable operation. A heat sink without a cooling fan may also be used. Damage caused from overheating will void the warranty.
- 3.) Confirm adequate system grounding is established. The DC power supply and Amplifier must have a common ground in order to operate properly.
- 4.) Power Amplifiers may require additional DC Current when initially powered-up. Depending on the design, the input current draw could range from an additional 10% to 100% above the maximum rated DC current of the Amplifier. This varies based on product part number.
- 5.) Confirm the DC power supply, if limited, is set to allow for additional start-up current that's rated for the Power Amplifier.
- 6.) Confirm the system is designed and calibrated for 50 ohms. Any impedance mismatch may cause performance issues.
- 7.) Perform a CALIBRATION (if required) with the loads before connecting the Amplifier to the Network Analyzer to ensure proper performance.
- 8.) Use a fixed attenuator between the signal source and input port of the Amplifier to optimize the input VSWR match.
- 9.) Confirm the input power (as stated in the Amplifier datasheet).
 - P_{in} for Small Signal Gain = P1dB-SSG-10 dB
 - P_{in} for P1dB = P1dB-SSG+1 dB
- 10.) Confirm the Network Analyzer is always connected to the Amplifier first before DC power is applied to the Amplifier.
- 11.) As long as the input and output ports of the amplifier are connected to a 500hm load and RF signal power is applied, the Amplifier can be powered up with DC voltage.
- 12.) Confirm the Amplifier output load is matched for a 50 Ohm impedance and will not exceed the maximum rated VSWR or Return Loss limit for the Amplifier. Exceeding the maximum rated VSWR or Return Loss limit will result in reflected signal power that could damage the Amplifier and void the warranty.
- 13.) Power Amplifier connected to an Antenna for signal transmission It's strongly recommended to use a high power fixed attenuator pad or an Isolator between the output port of the Amplifier and input port to the antenna. Any reflected signal power due to impedance mismatch will likely damage the Amplifier and void the warranty.
- 14.) The attenuator or isolator used at the output port of the Amplifier must be rated to handle the output power level and operational frequency band of the amplifier.


301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689






Functional Block Diagram











1.2 dB NF Input Protected Low Noise Amplifier, Operating from 2 GHz to 6 GHz with 40 dB Gain, 14 dBm P1dB and SMA from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 1.2 dB NF Input Protected Low Noise Amplifier, Operating from 2 GHz to 6 GHz with 40 dB Gain, 14 dBm P1dB and SMA FMAM63019

URL: https://www.fairviewmicrowave.com/1.2db-nf-low-noise-amplifier-40db-fmam63019-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





