


WR-430 90 Degree Waveguide Right Hand Twist Using a UG Cover And Grooved Flanges And a 1.72 GHz to 2.61 GHz Frequency Range



FMW430TW001

Features

- WR-430 Waveguide
- UG Cover and UG Grooved Flange
- 1.72 GHz to 2.61 GHz Frequency Ranges
- 90° Right Hand (Clockwise) Twist

Applications

- Instrumentation
- Precision Measurements
- Prototyping and Characterization
- Production Systems

Description

The FMW430TW001 is a 90 degree WR-430 waveguide twist that is part of a family of precision manufactured waveguide twists with UG Cover and UG Grooved flanges. The family includes right and left hand 45 degree twists as well as 90 degree twists. These twists are offered in the Ka through W waveguide bands (18 to 110 GHz).

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	1.72		2.61	GHz
VSWR		1.15:1		
Insertion Loss		0.2		dB

Mechanical Specifications

Waveguide Size WR-430
Section Length 15.75 in [400.05 mm]

Description	Flange 1	Waveguide	Flange 2
Flange Type	UG Cover		UG Grooved
Interface	UG	WR-430	UG
Material	Aluminum	Aluminum	Aluminum
Plating	Chromate Conversion	Chromate Conversion	Chromate Conversion
Color	Gray	Gray	Gray

Environmental Specifications


Temperature
Operating Range -40 to 70 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

WR-430 90 Degree Waveguide Right Hand Twist Using a UG Cover And Grooved Flanges And a 1.72 GHz to 2.61 GHz Frequency Range



FMW430TW001

Typical Performance Data

WR-430 90 Degree Waveguide Right Hand Twist Using a UG Cover And Grooved Flanges And a 1.72 GHz to 2.61 GHz Frequency Range from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [WR-430 90 Degree Waveguide Right Hand Twist Using a UG Cover And Grooved Flanges And a 1.72 GHz to 2.61 GHz Frequency Range FMW430TW001](https://www.fairviewmicrowave.com/wr-430-90-waveguide-twist-ug-1.72-2.61-ghz-fmw430tw001-p.aspx)

URL: <https://www.fairviewmicrowave.com/wr-430-90-waveguide-twist-ug-1.72-2.61-ghz-fmw430tw001-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMW430TW001 CAD Drawing

WR-430 90 Degree Waveguide Right Hand Twist Using a UG Cover And Grooved Flanges And a 1.72 GHz to 2.61 GHz Frequency Range

