

## 400 to 470 MHz, 3 dBi Exposed Dipole Antenna with N Female, Vertical Polarization, 1 Port, 1.5 VSWR

### FMANED1015



#### Features

- Frequency coverage for 400 MHz to 470 MHz with Type N Female connector and gain 3 dBi / 0.85 dBd antennas
- Multiple exposed dipoles can be mouted on a mast for best performance
- Feild adjustable radition patterns with 100W max input power per port
- Easy and quick time to installations with U-Bolt mounts
- Industrially tuned folded dipole allows plug and play
- Weather and corrsion free made of high-grade aluminum alloys
- Vertical Polarization

#### Applications

- Outdoor point-to-point (PtP) or point-to-multipoint (PtMP) applications
- UHF radio applications supported with Trunking for two-way radio communications
- Public Safety / Emergency services / Marine communications / Rail road communications
- Tetra and P-25 Applications exclusively supported
- Land Mobile Radio (LMR) and Private Mobile Radio (PMR)
- Fixed and mobile services for paging/voice/data in full duplex and half duplex mode

#### Description

Fairview Microwave's FMANED1014 3 dBi Exposed dipole antenna, with N female connector, is an economical yet high-Performance antenna designed for high-power applications. The Exposed dipole antenna's beamwidth can be adjusted according to applications by fixing dipoles at certain heights and directions. This high gain 3 dBi antenna transmits high-power signals, increasing the signal strength and thus providing improved coverage, better-broadcast control, and faster speed. This Exposed dipole antenna can output frequencies from 400 to 470 MHz, which is useful for military communications, trunking, public safety, industrial communication, and amateur radio applications.

Fairview Microwave's Exposed dipole antenna uses vertical polarization to transmit signals, thus reducing interference and performing better at lower heights. All components of this 3 dBi antenna are DC grounded for lightning protection, rugged outdoor design, and have a high-power handling capacity. The Exposed dipole antenna has 1 port to connect an external circuit with 100W maximum input power per port.

This Fairview Microwave's 400 to 470 MHz VHF/UHF antenna is one of the simplest and most widely used antenna producing radiation patterns like that of an electric dipole. FMANED1014 Exposed dipole antenna is a dipole stand-alone made of aluminum alloy, and thus packaging, transportation, and installation become easier. It has a 1.5 VSWR that results in the best power transfer and reduced losses. It comes with a threaded and weatherproof N female connector type which ensuring a reliable physical connection and can be fixed on a pole using the U-bolt brackets that come with the antenna.

FMANED1014 antenna with a 3 dBi maximum gain is ideal for LMR, military, airports, construction, mining, commercial applications, and radio users. This FMANED1014 Exposed dipole antenna from Fairview Microwave comes in compact packaging for lower shipping costs. Fairview Microwave's 400 to 470 MHz, 3 dBi Exposed dipole antenna with a N female connector is in stock and ready to ship the same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other Fairview Microwave products.

#### Configuration

Design	Dipole
Band Type	Single
Radiation Pattern	Omni Directional
Polarization	Vertical
Connector Type	N Female
Number of Ports	1
Lightning Protection	DC Ground

400 to 470 MHz, 3 dBi Exposed Dipole Antenna with  
N Female, Vertical Polarization, 1 Port, 1.5 VSWR

## FMANED1015



### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	400		470	MHz
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain			3	
Input Power			100	Watts

### Mechanical Specifications

Radome Material	Aluminum Alloy
<b>Size</b>	
Length	12.5 in [317.5 mm]
Width	12 in [304.8 mm]
Height	2 in [50.8 mm]
Weight	10.56 lbs [4.79 kg]

### Environmental Specifications

<b>Temperature</b>	
Operating Range	-40 to +80 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

400 to 470 MHz, 3 dBi Exposed Dipole Antenna with N Female, Vertical Polarization, 1 Port, 1.5 VSWR

## FMANED1015



### Typical Radiation Pattern

### Appendix

**Electrical Downtilt:** Angle in the antenna's elevation pattern in which the maximum gain occurs.

**Gain:** Antenna's average gain.

**Front to Back Ratio @  $180^\circ \pm 30^\circ$ :** Average difference between the antenna's maximum gain and the maximum gain in the antenna's back lobe over  $\pm 30^\circ$  angles.

**Cross-polarization Ratio (dB):** Typical difference between the co-polarization and cross-polarization gain across the sector's 3 dB Beam Width.

400 to 470 MHz, 3 dBi Exposed Dipole Antenna with N Female, Vertical Polarization, 1 Port, 1.5 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.




For additional information on this product, please click the following link: [400 to 470 MHz, 3 dBi Exposed Dipole Antenna with N Female, Vertical Polarization, 1 Port, 1.5 VSWR FMANED1015](https://www.fairviewmicrowave.com/product/antennas/dbi-antenna-400-470-mhz-n-type-connector-fmaned1015)

URL: <https://www.fairviewmicrowave.com/product/antennas/dbi-antenna-400-470-mhz-n-type-connector-fmaned1015.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

400 to 470 MHz, 3 dBi Exposed Dipole Antenna with N Female, Vertical Polarization, 1 Port, 1.5 VSWR

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	5/5/2022	KHIETPAS



1. LABEL PER ILS-100-03 (FOR INTERNAL REFERENCE ONLY).  
LABEL LOCATION FOR REFERENCE ONLY.



**Fairview Microwave**  
an INFINITE brand

SIZE <b>A</b>	CAGE CODE <b>3FKR5</b>	DRAWN BY <b>DMAY</b>	ITEM NO. <b>FMANED1015</b>	REV <b>A</b>
------------------	---------------------------	-------------------------	-------------------------------	-----------------