

QMA-M CONN LMR240 CRIMP

SC4852

SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0-6 GHZ
VSWR 1.3:1 MAX
IMPEDANCE: 50 OHMS
OP. TEMP RANGE: -55°C- +155°C


MECHANICAL:

MATERIAL BODY: ALBALOY PLATED BRASSS
CENTER CONTACT: BRASS GOLD PLATED 30μ"
INSULATOR: TEFLON

ROHS COMPLIANT

CABLES: LMR240 & LMR240 ULTRAFLEX
BELDEN 9258, RG-8/X

SOLDER INNER CONDUCTOR,
CRIMP OUTER CONDUCTOR



STRIPPING DIMENSIONS

RECOMMENDED CRIMP DIE: .255"

					FAIRVIEW MICROWAVE INC.	
					ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	
					TITLE	
					QMA-M CONN LMR240 CRIMP	
SIZE		CAGE CODE	DWG NO		REV	
A		3FKR5	SC4852		--	
SCALE			SHEET			