

2.92/F BULKHEAD .085 SEMI-RIGID

SC5831

SPECIFICATIONS

ELECTRICAL

50 OHMS

VSWR 1.25:1 MAX @ 40 GHZ

FREQUENCY: 0-40 GHZ

MECHANICAL

500 CYCLES MIN

4.0 INCH-OUNCES MIN CONTACT TORQUE

8-10 LBS COUPLING NUT MATING TORQUE

ENVIRONMENTAL

-55°C TO +100°C

CORROSION: MIL-STD 202

VIBRATION: MIL-STD 202


MATERIALS BODY: PASSIVATED STAINLESS STEEL

BODY: SST ASTM A484 / A582

CONTACTS: BeCu ASTM-B-196

CONTACTS PLATING: Au PER MIL-G-45204

ROHS COMPLIANT



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

2.92/F BULKHEAD .085 SEMI-RIGID

ALL DIMENSIONS IN inches(MM) Typical	SIZE	CAGE CODE	DWG NO	REV
	A	3FKR5	SC5831	--
	SCALE		SHEET	