



SMA/M-BNC/M FLEXIBLE CABLES 2GHZ LMR240


SCB18283-XX

SPECIFICATIONS


CABLE ASSEMBLY:
VSWR:1.2:1 @<2GHZ TYPICAL

RAW CABLE: LMR240
TYPICAL LOSS (EXCLUDING CONNECTORS)
@0.5GHz 0.06dB/ft
@1GHz 0.08dB/ft
@2GHz 0.11dB/ft
@3GHz 0.14dB/ft
@6GHz 0.21dB/ft
CONNECTORS:
BRASS
SMA torque 5-in-lbs
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55 to +110°C



MEASUREMENTS BELOW ARE TYPICAL



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M-BNC/M FLEXIBLE CABLES 2GHZ LMR240

SIZE

A

CAGE CODE

3FKR5

DWG NO

SCB18283-XX

REV

--

SCALE

SHEET

ALL DIMENSIONS IN inches(MM) Typical

