

SMA - SMA F/F FLANGE ADAPTER

SM4959

SPECIFICATIONS


ELECTRICAL

FREQUENCY: 0-18 GHZ
IMPEDANCE: 50 OHMS
VSWR: 1.20:1 MAX

MECHANICAL


MATERIALS BODY PASS. STAINLESS STEEL
MATERIALS CONTACTS: BeCu
PLATING Au MIL-G-45204
INSULATOR: TEFLON
DURABILITY: 500 CYCLES MIN
INTERFACE: MIL-STD-348

OPERATING TEMPERATURE; -55 to 100°C
ROHS COMPLIANT



MAX PANEL
THICKNESS .250"

MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA - SMA F/F FLANGE ADAPTER

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SM4959	D
SCALE			SHEET