






NON- PENETRATING PEAK ROOF MOUNT WITH OPTIONAL ARM ASSEMBLY INSTRUCTION 1/3


HARDWARE				TOOLS	PARTS							
NO	ITEM	DESCRIPTION	Q'TY		DESCRIPTION		Q'TY	DESCRIPTION		Q'TY		
1		5/16"-18*3-1/8" hex-head cap screw	3		Mast Pole(L850mm) (#A)		1	Adjustable rod (#C)		1		
2		5/16"-18 washer	8						E			
3		5/16"-18 nylon nut	4									
4		5/16"-18*7/8" Round head Square screw	1	13mm wrench (not included)		DESCRIPTION		Q'TY	DESCRIPTION		Q'TY	
5		5/16"-18*3/4" hex-head cap screw	1			Supporting rod (#B)		2				
6		5/16"-18 hex flange nut	1					D		F		
7		#12*3/4" Metal tek screw	1									
8		Link bracket	1									
9												
10												

NON- PENETRATING PEAK ROOF MOUNT WITH OPTIONAL ARM ASSEMBLY INSTRUCTION 2/3

INSTALLATION DESCRIPTION


Step 1

Assemble mast pole(#A) with screw(#1) , washer(#2),nylon nut(#3)




Step 2

Assemble 2 supporting rods(#B) with screw(#1) , washer(#2),nylon nut(#3)



Before assembly supporting rod ,release screw and nut then use same screw,washer and nut fixed




NON- PENETRATING PEAK ROOF MOUNT WITH OPTIONAL ARM ASSEMBLY INSTRUCTION 3/3

INSTALLATION DESCRIPTION



Step 3

Assemble Adjustable rod(#C) with screw(#1), screw(#5), washer(#2), nylon nut(#3)

Pre-assembly adjustable rod(#C) and link bracket(#8) with screw(#4), flange nut(#6)



inner rod rotate for fixed angle



Step 4

Adjust pole angel to 90 degree and tighten all screw, then fixed metal tek screw(#7) finally

